



- 1.CABLE: NO UL, 28AWG(7/0.127), TINNED AND STRANDED COPPER WIRE  
INSULATOR: PVC, ID: 0.85mm, CABLING: 9C+DRAIN WIRE  
SHIELD: AL/MY COVERAGE  
JACKET: PVC, COMPLIANCE ROHS, COLOR: BEIGE, O.D: 5mm
2. 1PCS CONNECTOR: D-SUB 25 WAYS MALE SOLDER TYPE CONNECTOR  
INSULATOR: P.B.T.+GLASS FIBER, COLOR: BLUE  
CONTACT: COPPER ALLOY, GOLD FLASH OVER NICKEL PLATED  
SHELL: NICKEL PLATED.  
CONNECTOR COMPLIANCE ROHS
3. 1PCS CONNECTOR: D-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR  
INSULATOR: P.B.T.+GLASS FIBER, COLOR: BLUE  
CONTACT: COPPER ALLOY, GOLD FLASH OVER NICKEL PLATED  
SHELL: NICKEL PLATED.  
CONNECTOR COMPLIANCE ROHS
4. HOOD: PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER  
ON INNER MOLD AND INJECTION OUTER MOLD WITH  
THUMB SCREW #4-40 & #4-48UNC  
COLOR: BEIGE, COMPLIANCE ROHS
5. Full ROHS Guideline
6. ELECTRONIC TEST: 100% OPEN SHORT+MISS WIRE TEST

PIN OUT

DB9 PIN FEMALE (J1)	WIRE	DB25 PIN PLUG (P1)
1	---	8
2	---	3
3	---	2
4	---	20
5	---	7
6	---	6
7	---	4
8	---	5
9	---	22
SHELL	DRAIN WIRE	SHELL

PART NO	SHEET NO	1	THIRD ANGLE PROJECTION
TITLE: DB9 PIN FEMALE TO DB25 PIN MALE BEIGE COLOR			SCALE: N.T.S.
			DRAWN BY & DATE
DWN NO: D-1051-XX			SIZE: A4
			CHECKED BY & DATE
			<input type="checkbox"/> mm
			<input type="checkbox"/> INCH
			APPROVED BY & DATE