

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0520450945](#)  
**Status:** **Active**  
**Overview:** ffc fpc throughhole  
**Description:** 1.25mm (.049") Vertical, Non-ZIF Receptacle, 9 Circuits

**Documents:**

[3D Model](#) [Product Specification PS-52045-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family FFC/FPC Connectors  
 Series [52045](#)  
 Overview [ffc fpc throughhole](#)  
 Product Name N/A

**Physical**

Circuits (Loaded) 9  
 Color - Resin Gray  
 Contact Position N/A  
 Entry Angle Vertical  
 Mated Height 8.00mm (.315")  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Material - Resin Polyester  
 Number of Rows 1  
 Orientation Vertical  
 PC Tail Length 3.50mm (.138")  
 PCB Retention None  
 Packaging Type Tray  
 Pitch - Mating Interface 1.25mm (.049")  
 Plating min - Mating 0.914µm (36µ")  
 Plating min - Termination 0.914µm (36µ")  
 Polarized to PCB Yes  
 Stackable No  
 Surface Mount Compatible (SMC) No  
 Temperature Range - Operating -40°C to +85°C  
 Termination Interface: Style Through Hole - Kinked Pin  
 Wire/Cable Type FFC/FPC


**Electrical**

Current - Maximum per Contact 0.5A, 1A  
 Voltage - Maximum 200V

**Material Info**

**Reference - Drawing Numbers**

Product Specification PS-52045-001, RPS-52045-003, RPS-52045-006  
 Sales Drawing SD-52045-\*\*45



**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[52045Series](#)