


ELECTRICAL TEST:
 1.100% OPEN SHORT SHORT & MIS WIRE TEST
 2.CONTACT RESISTANCE:2 OHM(MAX)
 3.INSULATION RESISTANCE:10M OHM(MIN)
 4.HI-POT TEST:DC 300V/10ms



13	A10-R075131	H.S.T: φ1.0*12mm Black	1	pcs
12	A78-0000154	Mini DP F(SHELL GOLD PLATED Insulation:Black) (10.5*15.5*1.5MM) emptyPCB+solder	1	pcs
11	A6-R104253	mini DisplayPort(SOLDER) F ABS UP SHELL SNOW WHITE	1	pcs
10	A6-R104254	mini DisplayPort(SOLDER) F ABS TOP SHELL SNOW WHITE	1	pcs
9	A10-R075132	H.S.T: φ1.5*5mm BLACK	5	pcs
8	A6-0000157	mini Display Port M DUST CAP	1	pcs
7	A6-R104240	mini DisplayPort(solder) M ABS UP SHELL SNOW WHITE	1	pcs
6	A6-R104239	mini DisplayPort(solder) M ABS TOP SHELL SNOW WHITE	1	pcs
5	A5-R047107	45P snow white PVC	8	9
4	A6-R021133	mini Display Port M Back shell nickel plated	1	pcs
3	A6-R021212	mini Display Port M Front shell gold plated	1	pcs
2	A2-R021292	mini DisplayPort M Insulation: WHITE PIN Gold plated, with PCB	1	pcs
1	A4-R001678	Display Port UL20276 [32AWG(7/0.08TC)*1PR+EAM]*5+32AWG(7/0.08TC)*5C +D(BC)+AB 85% (16/7/0.12AL) OD:4.8MM Snow white	2	m
		DESCRIPTION	Q'TY	UNIT

REV.	变更单编号	DESCRIPTION	DATE
	TOLERANCE INCHES		
DRAWN BY	.X	.015	.30
	.XX	.010	.10
	.XXX	.005	.05
CHECK BY		TITLE: MINI DP M TO MINI DP F CABLE GOLD 2M	
APPD BY		CUSTOMER: CD	
		CUSTOMER P/N: CDLMDP-402	
		SCALE: NONE	
		UNIT: MM	
		DATE: 2011.03.23	
			REV. A
			1/2