1	2	3	4	
38.76 ^{+0.76} 24.54 ^{+0.25} 24.54 ⁰ *0.18 ¢3.00 ⁻⁰	7.77 ^{0.25}			A
	<u>11.60,45,10,25</u> <u>6.05,02,25,40,25</u> <u>6.05,00,25</u> <u>7.25,40,25</u> <u>7.25,40,25</u> <u>7.25,40,25</u> <u>7.25,40,25</u> <u>7.25,40,25</u>	TIN LEAD PART Core n DA7W23 PART N	range SA00 UMBER	В
		LEAD FREE PART Core r DA7W2S PART N	nange AOOLF IUMBER	С
		GENERAL CHARACTERISTICS AND SEE DRAWING C01-8639-0003	D ROHS INFORMATIONS:	
27.25 ^{+0.51}	E LS05-005 MPE 3	Dr JARRY 1995/01/26 ANGULAR L date Eng PESSON 1995/01/26 ANGULAR L 2003/10/28 Chr LEGARE 1995/01/26 0.xx' ±2 2005/03/16 Appr LEGARE 1995/01/26 Product fa - - SOCKET CONNECTOR MARK - - CONTACTS catalog no	tolerance std ISO 406 ISO 1101 projection S UNLESS OTHERWISE SPECIFIED Imm 0.X ±0.1 0.XX ±0.1 A3 1.5 0.XXX ±0.1	D

А

В

С

U

Copyright FCI. U