



"W" DIM.	
GO	NO GO
.124	.130

Gage dimensions apply when tool is bottomed but not under pressure.

SUPERSEDED BY 15, 1412

1	D	306322-7	LINK	13
6	-	21095-6	RETAINING RING	12
2	A	300449	PIN	11
2	A	38716	SPACER	10
2	A	38380	TOGGLE LINK	9
1	A	38379	TOGGLE LEVER	8
1	A	300448	PIN	7
2	A	38384	PIN	6
1	D	306322-4	LINK	5
4	A	300102	RETAINING RING	4
1	A	38385	PIVOT PIN	3
1	B	49633	CRIMPING JAW-INDENTER	2
1	B	49632	CRIMPING JAW-NEST	1

DWG SIZE		NUMBER	NAME	REMARKS	ITEM NO
A		38923	HEAD ASSEMBLY		
©1998 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.					
DR		MATERIAL AND FINISH		CUSTOMER COPY REFERENCE ONLY	
CHK		CLASS		AMP INCORPORATED HARRISBURG, PENNA.	
DE		WIRE - RANGE - INSULATION		TYPE	
APP		TOLERANCE EXCEPT AS NOTED		LOC	
LTR		SCALE		NO	
REVISION RECORD		DATE		REV	
K SUP'D BY I.S. 1412		EJF EJF 9-22-64		M B 38923 K	
J-1 REVISED		PL 10-27-64			
J Redrawn		CM 8-22-64			

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.