

Dial calliper dialMax ESD, reading 0.1 mm.
Blister packed.



Material:	Calliper made of ESD-safe material. Non-metallic high-tech material with 60% fibre-glass content. Surface resistance $10^6 - 10^9$ ohms.
Scale:	Dial, diameter 35 mm.
Reading:	0.1 mm; 1 dial rotation represents 10 mm. Accuracy as per DIN 862.
Standards:	IEC 61340-5-1.
Application:	For all work with electrostatically endangered components. For outside, inside and depth measurements.
Extra:	Measurements in ESD protection zones and at ESD workstations. Impact resistant dial can be recalibrated to zero.

Ord.No.					Gross	Net
31439	150	6	45	5	42,10	18,95

The above-mentioned prices are in EUR.