

a vital part of your world

Text Search:

Wednesday, 11 January, 2006

CATALOG

→ Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- Part Number Search
- Document Search
- Product Type Search
- Product Family Search
- Alphabetical Search
- RoHS/ELV Compliance & Alternates
- CAD Model Search
- Brand Search
- Tool Search
- Multiple Part Comparison
- Lead Free Solutions
- Help/Glossary

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Economy Interconnection Products (EI and MT EI)

↳ **Crimp Termination (EI Series Connectors)**

AMP 170204-1 [Active](#)

Directive 2002/95/EC Compliant

[RoHS Compliant](#)

(Corporate P/N: 170204-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ➤ General Info ➤ Sales Info ➤ Assembly Subcontractors 	<ul style="list-style-type: none"> ➤ Pricing & Availability 	<ul style="list-style-type: none"> ➤ Tooling

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Contact
Contact Type:	Receptacle
Terminate To:	Wire
Special PCB Retention:	No
Wire Range (mm [AWG]):	0.14-0.52 ² [26-20]
Wire Insulation Diameter (mm [in]):	1.09 – 1.91 [0.043 – 0.075]
Contact Material:	Brass
Contact Mating Area Plating:	Pre-Tin
Packaging Method:	Loose Piece

Other Properties:	
RoHS/ELV Compliance History:	Always was RoHS compliant
For Use With:	Standard Profile Housing

Copyright and Privacy Statement
 Visit [Tyco International Ltd.](#)