

## Battery Operated Portable

Maxatec



H=93,  
W=106,  
D=209

- Battery operated hand held miniature printers
- Epson 'PU' series of impact printer mechanisms, 24 and 40 column printing at various print speeds of up to 2.5 lps
- Dot addressable graphics, double width, double height printing.
- Integral re-chargeable batteries, mains adaptor/charger is available
- Communication via serial RS232C

Parameters set externally using 'line feed' and 'on-line' buttons, eliminating the need for DIP switches

Ideal for a wide range of portable as well as static applications

Mfrs. List No.	Interface	Columns	Speed	Order Code
1012-0100-R	Serial	24	2.5	132-3436
1014-0100-R	Serial	40	1.8l	132-3438

206035

	Order Code	Price Each
Serial printer, 2.5 lps	132-3436 ●	
Serial printer, 1.8 lps	132-3438 ●	
Battery charger, UK version	132-3442 ●	
Battery charger, European version	132-3443 ●	

	Order Code	Price Each
Paper roll, 30m	231-952	

	Mfrs. List No.	Order Code	Price Each
Black Ribbon	IRC160B	440-8172	