

T&B® Fittings



T&B Catalog Number: 2921NM
UPC Number: 78621079741
Description: 1/2" Ranger®; Liquidtight Cord Connector-Straight. Body material-Weather stabilized nylon; Bushing-Rubber. Cord range-.310-.560
Status: Active

WEB_USE

-T&B Product Line 105

Features

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.

Application

- Provide a means for passing a cord cable into an enclosure through a bulkhead; Form a mechanical grip and water and/or oil-resistant seal for cord; Form a non-slip connection or termination for flexible cord and cable.

General

-Material Nylon
 -Cord and Cable Types S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

Dimension Information

-Hub Size (inches) 1/2
 -Dimension A (inches) 1 7/32
 -Dimension B (inches) 2 1/8
 -Dimension C (inches) 5/8
 -Cord Range (inches) .310-.560
 -Throat Diameter (inches) 0.55
 -Dimension A (inches) 1 7/32
 -Dimension B (inches) 2 1/8
 -Dimension C (inches) 5/8

Specifications

-3dmodel Available on Website

Packaging

-T&B Inner Pack 25
 -Package in Units 100
 -T&B Sold in UOM Each
 -T&B Weight Per UOM 5.2 lbs. per 100

Application Support

-T&B Instruction Sheets ta00927-tb2
 -Product Overview Available on Website
 -Specifications Available on Website
 -Liquidtight Flexible Cord and Cable Connectors-Application and Features Available on Website
 -Portable Cord Selection Table Available on Website

Notes

-**Note Suitable for Ordinary, Wet or Dry locations.

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com