



T&B Fittings

T&B Catalog Number: 3303-TB
UPC Number: 78621003303
Description: 3/4" Two Screw Connector, Steel-Electro Zinc Plated.

Status: Active

WEB_USE

-T&B Product Line 106

Features

- Rounded cable grip and smooth bushing protect the cable sheath and wire insulation. Since saddle is threaded, screws do not travel or extend beyond the connector body as it is clamped to the cable. An extra lip on the saddle closes the unused part of the connector opening.

Application

- To connect non-metallic sheathed cable and flexible cord to a box or an enclosure.

General

-Material Steel
 -Finish Electro Zinc Plated

Dimension Information

-Dimension A (inches) 1 1/4
 -Dimension B (inches) 1 5/8
 -Dimension C (inches) 1 1/4
 -Knockout Size (inches) 3/4
 -Cable Opening-Minimum (inches) 0.530
 -Cable Opening-Maximum (inches) 0.750
 -Dimension A (inches) 1 1/4
 -Dimension B (inches) 1 5/8
 -Dimension C (inches) 1 1/4

Specifications

-3dmodel Available on Website

Packaging

-T&B Inner Pack 50
 -Package in Units 250
 -T&B Sold in UOM Each
 -T&B Weight Per UOM 11.24 lbs. per 100

Application Support

-Product Overview Available on Website

Notes

-*Note U.L. listed and CSA certified for the following single (1) and pairs of (2) NM and NMC cable; (1) 2#8, 2#6, 3#8, 3#6, 3#4(2) 2#12, 2#10, 2#8, 3#14.
 -**Note U.L. listed and CSA certified for the following Service Entrance Cables; 2#8 thru 2#1/0, 3#8, 3#6, 2#6 + #8 GND, 2#1, 2#1/0, 3#6 thru 3#2.

Certifications

-RoHS Compliance Yes

Certifications



File Nbr:
E 17583

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com