




Sta-Kon®

T&B Catalog Number: RB14-10F
UPC Number: 78621080413
Description: Insulated Nylon Fork Terminal For Wire Range 18-14 Stud Size #10, Blue

Status: Active



WEB_USE

-T&B Product Line	029
-US Cutsheet PDF Catalog Link	http://www-public.tnb.com/contractor/docs/stakon.pdf

Features

-	Inner bronze insulation grip sleeve lengthens flex radius of conductor and eliminates conductor creep. Nylon jacket is color-coded.
---	---

General

-Insulation Type	Insulated Nylon
-Terminal Series	RB
-Material	Copper
-Finish	Electro -Tin Plated
-Color	Blue
-Wire Range	18-14
-Stud Size	#10

Dimension Information

-Maximum Insulation (inches)	.162
-Stock Thickness	.03
-A (inches)	.87
-B (inches)	.38
-C (inches)	.25
-M (inches)	.71

Specifications

-Temperature Rating	105°C
-Voltage Rating	600V
-Flammability Rating	UL 94 V-2

Tooling

-Tool Charts	Available on Website
-Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003, WT145A
-Recommended Tool	ERG4001

Packaging

-T&B Order Multiple	100
-T&B Inner Pack	100
-Package in Units	500
-Package Type	Standard
-T&B Sold in UOM	Each
-T&B Weight Per UOM	0.26 lbs. per 100
-Alternate Package Qty	RB1153

Application Support

-Overview	Available on Website
-Wire Guide Tables	Available on Website

Certifications

-RoHS Compliance Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com