




Sta-Kon®

T&B Catalog Number: RA2217
UPC Number: 78621081786
Description: Insulated Vinyl Locking Fork Terminal For Wire Range 22-16 Stud Size #6, Red

Status: Active



WEB_USE

-T&B Product Line	029
-US Cutsheet PDF Catalog Link	http://www-public.tnb.com/contractor/docs/stakon.pdf

Features

-	Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.
---	---

General

-Insulation Type	Insulated Vinyl
-Terminal Series	RA
-Material	Copper
-Finish	Electro -Tin Plated
-Color	Red
-Wire Range	22-16
-Stud Size	#6

Dimension Information

-Maximum Insulation (inches)	.150
-Stock Thickness	.03
-A (inches)	.97
-B (inches)	.25
-C (inches)	.25
-M (inches)	.81

Specifications

-Temperature Rating	105°C
-Voltage Rating	600V
-Flammability Rating	UL 94 V-0

Tooling

-Tool Charts	Available on Website
-Application Tools	ERG4001, ERG4003, WT145C, WT2000, WT112M, WT145C
-Recommended Tool	ERG4001

Packaging

-T&B Order Multiple	1000
-T&B Inner Pack	1000
-Package in Units	10000
-Package Type	Bulk
-T&B Sold in UOM	Each
-T&B Weight Per UOM	0.22 lbs. per 100
-Alternate Package Qty	18RA-6FL

Application Support

-Overview	Available on Website
-Wire Guide Tables	Available on Website

Notes

-

Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

Certifications

-RoHS Compliance

Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com