

# Sta-Kon®



**T&B Catalog Number:** RBB21  
**UPC Number:** 78621081951  
**Description:** Insulated Nylon Butt Splice Connector For Wire Range 16-14 Length 1.19 Diameter .21, Blue  
**Status:** Active

### WEB\_USE

-T&B Product Line -- 029  
 -US Cutsheet PDF Catalog Link -- <http://www-public.tnb.com/contractor/docs/stakon.pdf>

### Features

- -- Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.

### General

-Insulation Type -- Insulated Nylon  
 -Terminal Series -- RBB  
 -Material -- Copper  
 -Finish -- Electro -Tin Plated  
 -Color -- Blue  
 -Wire Range -- 16-14

### Dimension Information

-Maximum Insulation (inches) -- .148  
 -Stock Thickness -- .03  
 -A (inches) -- 1.19  
 -B (inches) -- .21

### Specifications

-Temperature Rating -- 105°C  
 -Voltage Rating -- 600V  
 -Flammability Rating -- UL 94 V-2

### Tooling

-Tool Charts Available on Website  
 -Application Tools -- ERG4001, ERG4003, WT145C, WT112M  
 -Recommended Tool -- ERG4001

### Packaging

-T&B Order Multiple -- 1000  
 -T&B Inner Pack -- 1000  
 -Package in Units -- 10000  
 -Package Type -- Bulk  
 -T&B Sold in UOM -- Each  
 -T&B Weight Per UOM -- 0.35 lbs. per 100  
 -Alternate Package Qty -- 2RB14

### Application Support

-Overview Available on Website  
 -Wire Guide Tables Available on Website

### Certifications

-RoHS Compliance -- Yes



### Certifications



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)