

Multimetrix®



Brand : [Multimetrix](#)

Manufacturer Ref. : X4010

Presentation

Analog oscilloscope, 10MHz bandwidth , 1channel, high quality CRT display, Auto/TV /Normal trigger mode, 400Vdc or ac max input voltage

Channel Count :	1 Channel
Bandwidth (Hz) :	10 MHz
Minimum Vertical Sensitivity (mV) :	5
Maximum Vertical Sensitivity (V) :	5 V
Mathematic functions (Y/N) :	No
Display :	CRT display
Dimension (HxWxD) (mm) :	215x85x278 mm
Net Weight (kg) :	3 kg