

White



Black



Specifications:

Material	: Nylon
Maximum operating temperature	: 100°C
Minimum operating temperature	: -20°C
Maximum panel thickness	: 3.5 mm
IP rating	: IP66

Specification Table

Colour	Maximum Cable Diameter	Minimum Cable Diameter	Projection Infront of Panel	Thread Length	Thread Size	Metric Thread Size	Part Number
Black	7	5	21	8	M13 × 1	M13	241/69/79B
	10.5	7	25	10	M16 × 1.5	M16	250/96/92B
	13	8	31	11	M20 × 1.5	M20	252/97/93B
	7	4	21	8			249/97/93B
	10.5	7	25	10			251/97/93B
White	7	5	21	8	M13 × 1	M13	241/69/79W
		4			M20 × 1.5	M20	249/97/93W
	10.5	7	25	10	M16 × 1.5	M16	250/96/92W
					M20 × 1.5	M20	251/97/93W
	13	8	31	11	M20 × 1.5	M20	252/97/93W

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2011.