

Main

Range of product	Harmony XAP
Product or component type	Die-cast empty control station
Device short name	XAPM
Product destination	For Ø 22 mm control and signalling units
Product front plate size	80 x 175 mm
Usable depth	74.5 mm
Number of cut-out	6 cut-outs
Number of vertical rows	2
Colour of base of enclosure	Blue
Colour of cover	Blue
Material	Zinc alloy
Product mounting	Flush mounting
IP degree of protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010

Complementary

Cable entry	1 hole with blanking plug for ISO 429248 cable gland 25 mm 1 hole without blanking plug for ISO 429248 cable gland 25 mm
Product weight	1.13 kg

Environment

Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Class of protection against electric shock	Class I conforming to NF C 20-030 Class I conforming to IEC 60536
RoHS EUR conformity date	0902
RoHS EUR status	Compliant