

Item # ZB5AVG1, Base & Light Module

Base & Light Module

Base & Light Module

SPECIFICATIONS

Product Description	Base & Light Module
Ampere Rating	N/A
Terminal Type	Screw Clamp
Wire Range	min: 1x0.22; max: 2x16AWG
Tightening Torque	0.8 Nm
Light Module Electrical Consumption	24V = 18mA; 120/240V = 14mA
CE	Yes
RoHS	Yes
Contact Configuration	n/a
Contact Material	n/a
Light Module Supply Voltage	110-120Vac
Light Module Type	LED(white)
Light Module Voltage	110-120Vac
Utilization Category	n/a
Used On	ZB5 Plastic Operators
Application	n/a