Panel Printer

AP1200





AP1200: H=67, W=115, D=104mm AP1200-12V: D=112mm

- Compact and stylish
 Easy paper-load system
 High speed and high quality fixed head thermal mechanism

Specification Print Method Number of columns Print Speed
Paper Width (mm)
Dots per line
Power Supply
Weight (including paper)

5V or 12V versions available
 Ideal for data recording applications
 Strong polycarbonate case

AP1200

AP1200-12V

AP1200 AP1200-12V Fixed head thermal 32 (default), 24 or 42 13 lines/sec (default character size) 50mm/second 57.5 ± 0.5 384 (3dots/mm)

5V to 8.5Vdc 315g

12V ± 10% 390g

419115

Mftrs. List No. Price Each Order Code 109-5840 109-5841 109-5842 AP1200 AP1200-12V Paper Roll, 22m