
Item no.: 280-675
Product description: 3-conductor double potential terminal block



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	18 A
Weight	12.4 g
Color	grey
Wiring type	Front-entry
No. of connection Points	6
No. of potentials	2
Height	28 mm
Height	1.1 in
Width	5 mm
Width	0.197 in
Depth	93 mm
Depth	3.66 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
280-675	BV	07436/C0			0,08-2,5
280-675	UR	E45172	600	10	28-16

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected