


VPJ CONNECTOR

5.0mm pitch/Disconnectable Crimp style connectors



Compact, Water Resist and Durable. This connector for electrical connection can be used on both waterproof and nonwaterproof conditions, depending on the usage. Just by placing a rubber part will change it into a water resistant connector. Both conditions are using the same header.

- Waterproof Performance [Grade 7 ingress protection of JIS C 0920 (IEC 60529 IPX7)]
- Control Key System
- Contacting part of contact is hardly deformed
- Inner-housing lock
- Compact Design

Specifications -

• Current rating: 7A AC, DC (AWG #18)

· Voltage rating: 300V AC, DC

• Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

Contact resistance: Initial value/10m Ω max.

After environmental testing/20m Ω max.

 Insulation resistance: 1.000M Ω min. • Withstanding voltage: 1,500V AC/minute

• Applicable wire: Conductor size/AWG #22 to #18 Insulation O.D./2.32 to 2.83mm

1.52 to 2.03mm

· Waterproof grade: Grade 7 ingress protection of JIS C 0920(IEC 60529 IPX7)

- * RoHS compliant products are published. * Refer to "General Instruction and Notice when using
- Terminals and Connectors" at the end of this catalog.
- * Contact JST for details.


Standards -


Recognized E60389

⊕ Certified LR20812

△ File No.R50073100

PC board layout (viewed from component side) and Assembly layout






Note: 1. Tolerances are non-cumulative: ±0.05mm for all centers.

2. The dimensions above should serve as a guideline. Contact JST for details.

WPJ CONNECTOR

(Non-waterproof type)

Contact



Model No.	Applicable wire		Insulation O.D. (mm)	0/4/1
	mm²	AWG#	Insulation O.D. (mm)	Q'ty / reel
SWPJR-21T-M0.5	0.33~0.83 22~18		2.32~2.83	4,500
*SWPJR-21T-M0.5A	0.33~0.83	22~18	1.52~2.03	4,500

Material and Finish


Copper alloy, tin-plated (reflow treatment)

RoHS compliance

Note: *Marked product is not UL/CSA/TÜV approved.

Contact	Crimping		Applicator			
Contact	machine	Crimp applicator	Dies	Crimp applicator with dies		
SWPJR-21T-M0.5	AP-K2N	MKS-L	MK/SWPJR/T-21-05	APLMK SWPJR/T21-05		
		_	_	_		
SWPJR-21T-M0.5A		MKS-L	MK/SWPJR/T-21-05A	APLMK SWPJR/T21-05A		
		_	_	_		

Housing



Receptacle housing

-				
Circuits	Model No.	Α	В	Q'ty / bag
2	WPJR-02V-1-S	_	12.1	1,000
3	WPJR-03V-1-S	10.0	17.1	1,000

Material

Glass-filled PBT, UL94V-0, natural (white)


RoHS compliance

<For reference> Polarizing key pattern

Key pattern No.1(Color: Natural): WPJR-02V-1-S Key pattern No.2(Color: Red): WPJR-02V-2-R Key pattern No.3(Color: Blue): WPJR-02V-3-E

For availability, delivery and minimum order quantity, contact JST.

Header



Circuits	Model No.	Α	В	Q'ty / bag
2	B02B-WPJSS-1	_	14.2	400
3	B03B-WPJSS-1	10.0	19.2	300

Material and Finish

Wafer: Glass-filled PBT, UL94V-0 Post: Copper alloy, copper-undercoated, tin-plated (reflow treatment)

RoHS compliance This product displays (LF)(SN) on a label.

<For reference> Polarizing key pattern


Key pattern No.1(Color: Natural): B02B-WPJSS-1 B02B-WPJRS-2 Key pattern No.2(Color: Red): B02B-WPJES-3 Key pattern No.3(Color: Blue):

For availability, delivery and minimum order quantity, contact JST.

WPJ CONNECTOR

(Waterproof type)

Contact



Model No.	Applicable wire		Insulation O.D. (mm)	014/1	
	mm ²	AWG#	Insulation O.D. (mm)	Q ty / reer	
SWPJR-21T-M0.5	0.33~0.83	22~18	2.32~2.83	4,500	


Material and Finish

Copper alloy, tin-plated (reflow treatment)

RoHS compliance

Contact	Crimping	Applicator			
Contact	machine	Crimp applicator Dies		Crimp applicator with dies	
SWPJR-21T-M0.5	AP-K2N	MKS-L	MK/SWPJR/T-21-05	APLMK SWPJR/T21-05	
3WF3K-211-W0.3		_	_	_	

Housing



Receptacle housing assembly

Circuits	Model No.	Α	В	Q'ty / box
2	02R-WPJV-1-SMM	-	12.1	240
3	03R-WPJV-1-SMM	10.0	17.1	192

Material

Receptacle housing: Glass-filled PBT, UL94V-0, natural (white) Seal ring: Silicon, green Seal rubber plate: Silicon, green


RoHS compliance

<For reference> Polarizing key pattern

Key pattern No.1(Color: Natural):02R-WPJV-1-SMMKey pattern No.2(Color: Red):02R-WPJV-2-RMMKey pattern No.3(Color: Blue):02R-WPJV-3-EMM

For availability, delivery and minimum order quantity, contact JST.

Header



Circuits	Model No.	Α	В	Q'ty / bag
2	B02B-WPJSS-1	-	14.2	400
3	B03B-WPJSS-1	10.0	19.2	300

Material and Finish

Wafer: Glass-filled PBT, UL94V-0

Post: Copper alloy, copper-undercoated, tin-plated (reflow treatment)

RoHS compliance This product displays (LF)(SN) on a label.

<For reference> Polarizing key pattern

Key pattern No.1(Color: Natural):B02B-WPJSS-1Key pattern No.2(Color: Red):B02B-WPJRS-2Key pattern No.3(Color: Blue):B02B-WPJES-3

For availability, delivery and minimum order quantity, contact JST.