



**LED**

LED TYPE:

FEATURES:

BATTERY TYPE:

ACCESSORIES:

SIZE:

WEIGHT:

**SPECIFICATION**

- 160 Lumen white CREE LED
- Beamaster Lens for Ultimate beam penetration
- Hi-Visibility Yellow for added safety
- Rubber moulded micro switch
- Side charging point for rechargeable battery use
- Ease change screw cap for battery replacement
- Flexible rotational lantern head 135°
- Made from robust Industrial strength Copolymer
- Impact Resistant to 1M
- Water Resistant
- 1 x 2000mAh Rechargeable 6v Lantern battery (Included)
- Mains charger & 12/24V in car charger
- Mounting wall bracket & Carry strap
- 250mm x 110mm
- 420g (With Battery)

LIGHT BY  
**CREE**  
LED Light

MODE	ON
Measured Output	160 LUMENS
Beam Intensity	3300cd
Beam Distance	135m
Battery Life	10h
1m Impact Resistance	✓
IPX4	✓

PS-RB2  
Rechargeable Lantern battery  
to be used with either the  
PS-MC or PS-VC

Mounted Wall Bracket  
(Included)



PS-MC  
Mains charger for  
PS-RB2



PS-VC  
12/24v Vehicle charger for  
PS-RB2



TAILORED GRIP HANDLE

MICRO SWITCH



INDUSTRIAL COPOLYMER BODY

**BEAMMASTER**  
LENS