





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L2	REVISED PER ECR-09-012310	04JUN2009	HMR	KR

- MATERIAL: NYLON, UL94V-2 (NATURAL).
2. MARKING FOR UL AND CSA LOGO SHALL BE LOCATED ON ANY EXTERNAL SURFACE.
- AMP LOGO AND CIRCUIT NUMBERS LOCATED IN AREA, EITHER SIDE, SIZE OPTIONAL, FROST BACKGROUND.
- WALL THICKNESS TO MEASURE 0.36-0.46 [.014-.018]
- MATERIAL: NYLON 4/6, NATURAL.
- PRELIMINARY - NOT FOR PRODUCTION.



	770070-2
	770070-1
MATERIAL	PART NUMBER

TYPICAL DIMENSIONS TO DIMENSIONS SPECIFIED FOR THIS ELECTRONIC COMPONENT TYPICAL DIMENSIONS TO DIMENSIONS SPECIFIED FOR THIS ELECTRONIC COMPONENT TYPICAL DIMENSIONS TO DIMENSIONS SPECIFIED FOR THIS ELECTRONIC COMPONENT		DWN R. WHITAKER 03AUG2004	Tyco Electronics Harrisburg, PA 17105-3608	
CHK D. COLEY 03AUG2004		APVD D. COLEY 03AUG2004	NAME	
DIMENSIONS: mm [INCHES]		PRODUCT SPEC	RECEPTACLE, 3 CIRCUIT, .093 COMMERCIAL PIN AND SOCKET	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
0 PLC ±		WEIGHT	A100779C=770070	
1 PLC ±		CUSTOMER DRAWING	RESTRICTED TO	
2 PLC ±0.13 [.005]			SCALE 5:1 SHEET 1 OF 1 REV L2	
3 PLC ±				
4 PLC ±				
ANGLES ±				
FINISH ±				

METRIC