

**Productname :** OFFICECLEAN lingettes  
**Ref.Nr.:** BB45870-3-231110  
**Creationdate :** 23.11.10  
**Replaces:** 14.06.10

## 1. IDENTIFICATION OF PRODUCT AND COMPANY

**Productname :** OFFICECLEAN lingettes  
Bulk

**Application :** Cleaning - Accessories

**Company :** CRC Industries Europe bvba  
Touwslagerstraat 1  
9240 ZELE  
Belgium  
Tel.: (+32)(0)52/456011  
Fax: (+32)(0)52/450034  
E-mail : [hse@crcind.com](mailto:hse@crcind.com)

**In case of emergency :** (+32) (0)52/45 60 11

Subsidiaries		Tel	Fax
CRC Industries Finland	Asemanrinne 13, 08500 Lohja AS	(+358)(0)19/32921	(+358)(0)19/383676
CRC Industries France	12, Bld des Martyrs de Chateaubriant F-95102 Argenteuil Cédex	(+33)(0)1/34112000	(+33)(0)1/34110996
CRC Industries Deutschland	Südring 9, 76473 Iffezheim	(+49)(0)7229/3030	(+49)(0)7229/303266
CRC Industries Iberia	Gremio del cuero S/N, 40195 Segovia	(+34)921/427546	(+34)921/436270
CRC Industries Sweden	Kryptongatan 14, 43153 Mölndal	(+46)(0)31/7068480	(+46)(0)31/273991

## 2. HAZARD IDENTIFICATION

**Health and Safety :** Flammable  
Vapours may cause drowsiness and dizziness.

**Environment :** According to EU-directive 99/45/EC not classified

## 3. COMPOSITION AND INFORMATION ON COMPONENTS

Hazardous ingredient	CAS-nbr.	EINECS	w/w %	symbol	R-phrases*	Notes
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	203-539-1	<15		R10,R67	A
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	0-20	F,Xi	11-36-67	B
<b>Explanation notes</b>						
A : substance with Community workplace exposure limit						
B : substance with national established workplace exposure limit						

(\* Explanation risk-phrases : see chapter 16)



<b>Productname :</b>	OFFICECLEAN lingettes	<b>Creationdate :</b>	23.11.10
<b>Ref.Nr.:</b>	BB45870-3-231110	<b>Replaces:</b>	14.06.10

#### 4. FIRST AID MEASURES

<b>General Advice :</b>	If symptoms persist always call a doctor
<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
<b>Contact with skin :</b>	Wash with water and soap. Seek medical attention if irritation persists
<b>Inhalation :</b>	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
<b>Ingestion :</b>	Ingestion is unlikely to occur If swallowed accidentally, do not induce vomiting and seek medical advice.

#### 5. FIRE-FIGHTING MEASURES

<b>Flash point (without propellant):</b>	28 °C
<b>Explosion limits : upper limit :</b>	Not available.
<b>lower limit :</b>	Not available.
<b>Extinguishing media :</b>	foam, carbon dioxide or dry agent
<b>Fire-fighting procedures :</b>	Keep container(s) exposed to fire cool, by spraying with water

#### 6. ACCIDENTAL RELEASE MEASURES

<b>Personal precautions :</b>	Shut off all ignition sources Ensure adequate ventilation Wear suitable protective clothing including eye/face protection.
<b>Environmental precautions :</b>	Do not allow to enter public sewers and watercourses
<b>Cleaning methods :</b>	Absorb spillage in suitable inert material

#### 7. HANDLING AND STORAGE

<b>Handling procedures :</b>	The usual precautions for handling chemicals should be observed Keep away from heat and sources of ignition Avoid contact with skin and eyes.
<b>Storage procedures :</b>	Keep in a cool, dry, well ventilated place Keep out of reach of children.

#### 8. EXPOSURE CONTROL AND PERSONAL PROTECTION

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition
-----------------------------	--



**Productname :** OFFICECLEAN lingettes      **Creationdate :** 23.11.10  
**Ref.Nr.:** BB45870-3-231110      **Replaces:** 14.06.10

**Personal protection :** The usual precautions for handling chemicals should be observed  
It is advisable to take precautions to avoid contact with skin and eyes when handling the product.

**Exposure limits :**

Hazardous ingredient	CAS-nbr.	method	
<b>EU established exposure limits:</b>			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm

**9. PHYSICAL AND CHEMICAL PROPERTIES (for aerosols without propellant)**

**Apperance : physical state :** Paper tissue impregnated with liquid.  
**colour :** White.  
**odour :** Alcohol.  
**Boiling point/range :** Not available.  
**Relative density :** 0.85-0.95 g/cm<sup>3</sup> (@ 20°C).  
**pH :** Not applicable.  
**Vapour pressure :** Not available.  
**Relative vapour density :** Not available.  
**Solubility in water :** Soluble in water  
**Flash point :** 28 °C  
**Auto-ignition :** > 200 °C  
**Viscosity :** Not available.  
**Evaporation rate :** Not available.

**10. STABILITY AND REACTIVITY**

**Conditions to be avoided :** Avoid overheating  
**Materials to be avoided :** Strong oxidising agent  
**Hazardous decomposition compounds :** CO,CO<sub>2</sub>

**11. TOXICOLOGICAL INFORMATION**

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
Symptoms : sore throat, cough, shortness of breath, headache  
**Skin contact :** Prolonged skin contact will result in defatting of the skin  
**Eye contact :** Irritating to eyes  
Symptoms : redness and pain, impaired vision



<b>Productname :</b>	OFFICECLEAN lingettes	<b>Creationdate :</b>	23.11.10
<b>Ref.Nr.:</b>	BB45870-3-231110	<b>Replaces:</b>	14.06.10

## 12. ECOLOGICAL INFORMATION

Do not allow to enter public sewers and watercourses

## 13. WASTE DISPOSAL

**Product :** Do not empty into drains.  
This material and its container must be disposed of in a safe way.  
Disposal should be in accordance with local, state or national legislation

## 14. TRANSPORT

<b>UN-number :</b>	3175
<b>Road/Rail - ADR/RID :</b>	UN3175 Solids containing flammable liquid, n.o.s. (propan-2-ol, 1-methoxy-2-propanol) Class : 4, PG : II, Class code : F1, Label : 4.1, Tunnel-code : (E)
<b>Sea - IMDG :</b>	UN3175 Solids containing flammable liquids, n.o.s. (propan-2-ol, 1-methoxy-2-propanol) Class : 4, PG : II, Label : 4.1
<b>EmS</b>	F-A, S-I
<b>Air - IATA/ICAO :</b>	UN3175 Solids containing flammable liquids, n.o.s. (propan-2-ol, 1-methoxy-2-propanol) Class : 4, PG : II, Label : RFS

## 15. REGULATORY INFORMATION

**Risk-phrase(s) :** R10: Flammable.  
R67: Vapours may cause drowsiness and dizziness.

**Safety-phrase(s) :** S2: Keep out of the reach of children.  
S16: Keep away from sources of ignition - No smoking.  
S24/25: Avoid contact with skin and eyes.  
S26: In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

<b>Productname :</b>	OFFICECLEAN lingettes	<b>Creationdate :</b>	23.11.10
<b>Ref.Nr.:</b>	BB45870-3-231110	<b>Replaces:</b>	14.06.10

**16. OTHER INFORMATION**

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

**REVISIONS IN CHAPTRE :** 2,3

**\*Explanation risk-phrases:**  
R11: Highly flammable.  
R36: Irritating to eyes.  
R67: Vapours may cause drowsiness and dizziness.

This Material Safety Data Sheet may already have been revised at this moment for reason such as legislation, availability of components and newly acquired experiences. The latest and only valid version of this Material Safety Data Sheet will be sent to you upon simple request or can be found on our website : [www.crcind.com](http://www.crcind.com). We recommend you to register on this website for this product so you will be able to receive any future updated version automatically.

