



BU-00000- *
Part # color

* 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

CLIPS & INSULATORS



[Enlarge](#)

BU-34 Steel Micro-Alligator 5 Amp
BU-34C Solid Copper Micro-Alligator 5 Amp

- Smooth jawed clip has a microscopic tip
- Nose width is 0.0625" (1.6mm)
- Solder or crimp connection
- 7/32" (5.6mm) max. jaw opening
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-36 Insulator for BU-34/34C

- Skin-tight flexible vinyl
- Available in black, red, yellow, green, blue and white
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)



[Enlarge](#)

BU-30 Steel Miniature-Alligator 5 Amp
BU-30C Solid Copper Miniature-Alligator 5 Amp

- Full meshing teeth
- Jaw opens 3/16" (4.8mm) max.
- Solder or crimp connection
- 7/32" (5.6mm) jaw opening
- Federal spec.: Type TCM-1-W-C-440B(BU-30C)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-32 Insulator for BU-30/30C

- Skin-tight flexible vinyl
- Available in black, red, yellow, green, blue and white
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

[Contents](#) | [Next](#)

[Home](#) | [Insulated BNCs](#) | [Test Leads](#) | [Insulated Test Accessories](#)
[Accessories & Probes](#) | [Kits](#) | [Cross Reference](#)