







BU-30BL Miniature-Alligator with Barrel 5 Amp



- Full meshing teeth
- Rolled barrel tail section
- Steel
- Solder or crimp connection
- 3/16" (4.8mm) maximum jaw opening
- Product Data Sheet
- Send us your questions about this product

BU-30TBO Miniature Alligator with Threaded Barrel - 5 Amp

- Steel with threaded steel barrel
- Connects to any 6-32 threaded male test prod
- Product Data Sheet
- Send us your questions about this product



Enlarge



BU-31 Insulator for BU-30BL or BU-30TBO



- · Available in black, red, yellow, green, blue and white
- Product Data Sheet
- Send us your questions about this product

Alligator Clip with Barrel 10 Amp: BU-60 (Steel) BU-60C (Solid Copper) BU-60X (Stainless Steel)

- Standard clip with barrel for a banana plug
- Solder or crimp connection
- 5/16" (7.9mm) max. jaw opening
- Nose width 0.13"
- Stainless steel clip, body, rivet and spring
- Product Data Sheet
- Send us your questions about this product



Enlarge

Insulated BNCs|Test Leads|Insulated Test Accessories Accessories & Probes|Kits|Cross Reference

©2003 Mueller Electric Company. All rights reserved. Problems with the site should be reported to the webmaster.