

NEW
From Wiha

Wiha ESD Safe Proturm Pliers & Cutters

Surface resistance of handles is $10^6 - 10^9$ Ohms

Proturm available Spring 2010

ESD Safe Diagonal Cutter



458 23 Proturm ESD Safe 21° Precision Cutters/Flush Cut
ESD standard IEC 61340-5-1. C70 special tool steel. Glare free, black finish. ESD Safe handle with non-slip grips.

#458 23	mm	Inch	AWG	A	B	C	Pkg.	wt.
	133	5.25	14/1.6mm	10mm	10mm	2mm	1	.14

ESD Safe Diagonal Cutter



458 24 Proturm ESD Safe 45° Precision Cutters/Flush Cut
ESD standard IEC 61340-5-1. C70 special tool steel. Glare free, black finish. ESD Safe handle with non-slip grips.

#458 24	mm	Inch	AWG	A	B	C	Pkg.	wt.
	140	5.5	14/1.6mm	13mm	12mm	2.5mm	1	.16

proturm



NEW
From Wiha

Surface resistance of handles is $10^6 - 10^9$ Ohms



ESD standard IEC 61340-5-1

458 90 26 Pc. Set, Proturm ESD Safe Pliers, Precision Slotted & Phillips Screwdrivers, Precision Micro Bit Set & ESD Safe Tweezers

ESD Proturm Pliers glare free, black finish, ESD Safe non-slip soft grips. ESD Safe Precision Slotted & Phillips screwdrivers, CVM tool steel blades. Precision ESD Safe Micro Bit handle holds Micro Bit extension and 4mm Micro bits. Anti-static Tweezer conductive, ESD Safe Hypo allergenic, anti-magnetic stainless.

#458 90 26 Piece ESD Safe Pliers, Precision Screwdrivers, Micro Bit Set & ESD Tweezer In Custom Case Includes:

ESD Safe Proturm Strippers, Pliers & Cutters	
45810 6.5" Wire Stripper	45811 6.3" Long Nose Pliers
45813 6.0" Bent Nose Pliers	45823 5.25" 21° Precision Cutters

ESD Safe Slotted & Phillips Precision Screwdrivers	
Slotted: 2.0, 2.5, 3.0mm	Phillips: 0, 1

ESD Micro Bit Handle, Micro Bit Extension & 14 Micro Bits 4mm
Hex: .71, .89, 1.27, 1.5, 2.0, 2.5, 3.0 Torx: T4, T5, T6, T7, T8, T9, T10

ESD Safe Tweezer: 44532 00 SA ESD - 120mm Heavy Duty Strong, Tapered To Strong Point.

Weight: 2.05 lbs.