
Item no.: 280-618
Product description: Terminal block for pluggable modules orange separator 2-conductor terminal blocks 12 mm / 0.468 in wide



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	10 A
Weight	11.442 g
Color	grey
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	2
Height	28 mm
Height	1.1 in
Width	12 mm
Width	0.472 in
Depth	50 mm
Depth	1.97 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
280-618	BV	07436/C0			0,08-2,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected