

Roebuck



Adjustable pliers for gripping pipes, nuts and bolts

Four types of joint available - slip, groove, box joint and one-hand operation box (Grip Star)

Groove joints are recommended for heavier duty applications

Box joints are the strongest

Not insulated

Associated Products	212147
Handle type	Vinyl Grip
Jaw type	Slip
Length	250 mm
Length, Inches	10 "
RoHS Compliant	NA