

SAFETY DATA SHEET CONTACT CLEANING STRIPS

1 IDENTIFICATION OF THE MATERIAL AND SUPPLIER

PRODUCT NAME	CONTACT CLEANING STRIPS
PRODUCT NO.	ECCS020
APPLICATION	Cleaning Product
SUPPLIER	H K WENTWORTH PTY LIMITED P.O. BOX 339 BROOKVALE, NSW 2100 AUSTRALIA TEL: 02 9938 1566 FAX: 02 9938 1467 GENERAL MANAGER
EMERGENCY TELEPHONE	Tel: 029938 1566 between 8.30am and 5.00pm EST

2 HAZARDS IDENTIFICATION

HAZARD ID

Not regarded as a health or environmental hazard under current legislation.

HAZARD ID 2

The above phrases are the risks associated with the product

STATEMENT OF HAZARDOUS NATURE

NON-HAZARDOUS SUBSTANCE (According to criteria of NOHSC). NON-DANGEROUS GOODS (According to ADG Code).

SAFETY PHRASES

NC Not classified.

DG CLASS

Not classified for transportation.

3 COMPOSITION/INFORMATION ON INGREDIENTS

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels. Ingredients are registered on AICS.

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Provide rest, warmth and fresh air.

INGESTION

Rinse mouth thoroughly. Get medical attention.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

6 ACCIDENTAL RELEASE MEASURES

CONTACT CLEANING STRIPS

SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact.

STORAGE PRECAUTIONS

Store in tightly closed original container in a cool, dry well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

INGREDIENT COMMENTS

Australian exposure limits are: LT= ES-TWA and ST= ES STEL

ENGINEERING MEASURES

No particular ventilation requirements.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

If risk of splashing, wear safety goggles or face shield.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of skin contact.

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE

Oily Liquid

ODOUR

No characteristic odour.

FLASH POINT (°C)

>200 CC (Closed cup).

AUTO IGNITION TEMPERATURE (°C) >300 C)

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid excessive heat for prolonged periods of time.

11 TOXICOLOGICAL INFORMATION

HEALTH WARNINGS

No specific health warnings noted.

No specific acute or chronic health impact noted, but this chemical may still have adverse impact on human health, either in general or on certain individuals with pre-existing or latent health problems.

Other Health Effects

This substance has no evidence of carcinogenic properties.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Not regarded as dangerous for the environment.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

