




Revision	CN Number	Date	By	App'd
A	1st Issue	17.9.01	IJ	NW



WIRING CONFIGURATION

PIN No	
1	GREY/PINK
2	WHITE/GREEN
3	WHITE/YELLOW
4	BROWN
5	BROWN/YELLOW
6	BLUE
7	YELLOW
8	GREEN
9	PINK
10	WHITE
11	RED/BLUE
12	BROWN/GREEN
13	GREY
14	RED

VIEW FROM FRONT



PART No MATRIX

1	0	C	0	0	0	X	7	8	X	X	X	X	X
1=Mini Change A-Size	0=Portable	14 - PIN	000 = Female Straight			E=PVC P=PUR	78=2x0.75mm+12x0.34mm		M=Metres F=Feet	LENGTH 020=2 METRES 050=5 METRES 200=20 METRES			Blank=Yellow (Standard) A=Grey G = Black
Coupling Nut Material Blank=Standard 1=Stainless Steel 5=Delrin													

A4	MATERIAL:		<i>Tolerances:</i> <u>Linear</u> 0 = ±0.5mm (0.02") 0.0 = ±0.25mm (0.01") 0.00 = ±0.1mm (0.005") <u>Cable Lengths</u> Less than 5m = ±25mm More than 5m = ±50mm <u>Angular</u> ±1.0°	DRAWN	I.Jenkins	TITLE :- MC-14P-FE/ST	SCALE NTS
	FINISH :			DATE	17.9.01		
 3rd ANGLE PROJECTION	 Woodhead Connectivity Ltd FACTORY 9 RASSAU IND. EST. EBBW VALE GWENT NP23 5SD THIS DRAWING IS THE PROPERTY OF WOODHEAD CONNECTIVITY LTD. THE INFORMATION CONTAINED IS CONFIDENTIAL AND MUST NOT BE DISCLOSED			CHK'D	N. W.	PART NO: 10C000XXXMXXX	REVISION 