

6

5

4


3

2

1

NOTES:

1 PRODUCT LABELED & PACKAGED COMPLETE

2 CATALOG NUMBER, AMP & VOLTAGE RATING, DATE CODE, AND
WOODHEAD LOGO, TO BE PRINTED ON CABLE.

PART No.	CABLE LENGTH
L04301M78M050	5 METER
L04301M78M100	10 METER

REMOVE LOGO/UPDATE MOLD
EC NO: WNA2010-0108
DRWN: LHARTMAN 8/17/09
CHKD: TWOLDEGE2009/09/22
APPR: JFMURPHY 2009/10/26

QUALITY
SYMBOLS
▽=0
▽C=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
INCH/MM

DRAWN BY	DATE
QW	1998/10/19
CHECKED BY	DATE
BP	1998/10/19
APPROVED BY	DATE
JFMURPHY	2009/10/23
MATERIAL NO.	SEE TABLE
SIZE	A

SCALE
1:1DESIGN UNITS
INCHTHIRD ANGLE
PROJECTION

TITLE
M16 HOME RUN CABLE
14 POLE FEMALE 90 DEGREE

MOLEX INCORPORATED

DOCUMENT NO. L04301M

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

6

5

4

3

2

1