

F


E

D

C

B

A



Pin	Kolor przew.	Wire color
1	SZARO/ROZOWY	GY/PK
2	BIALO/ZIELONY	WH/GN
3	BIALO/ZOLTY	WH/YE
4	BRAZOWY	BN
5	BRAZOWO/ZOLTY	BN/YE
6	NIEBIESKI	BU
7	ZOLTY	YE
8	ZIELONY	GN
9	ROZOWY	PK
10	BIALY	WH
11	CZERWONO/NIEBIESKI	RD/BU
12	BRAZOWO/ZIELONY	BN/GN
13	SZARY	GY
14	CZERWONY	RD





TABELA 1
CHART 1

MOLEX PN	WOODHEAD PN	L(mm)	TOLERANCE[MM]
1300135005	1RCD36E78C4003	400	±25
1300138027	1RCD36E78M0203	2000	±25
1300150188	1RCD36E78C2003	200	±25
1300150189	1RCD36E78C5003	500	±25



UWAGI:

1. DŁUGOŚCI CIECIA I SPECYFIKACJE NABIJANIA WG LISTY CIECIA.

NOTES:

1. CUTTING LENGHT AND CRIMPING SPECIFICATION IN CUTTING LIST.

ORIGINAL RELEASE EC NO: DRWN:MWOLSZCZAK2008/08/02 CHKD: APPR:	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION ⊙ □			
				mm	INCH	DRAWN BY MWOLSZCZAK	DATE 2008/08/02	TITLE MC-14P-MM-REC -PG13.5-XM-PVC				
						CHECKED BY	DATE					
						APPROVED BY KOTYPKO	DATE 2008/08/02	moLEX MOLEX INCORPORATED				
						MATERIAL NO. SEE NOTE 1	DOCUMENT NO. 1RCD36XXXXXXX					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					