



SIDE: A





Farnell NO.	8706700	8706719	8706727
L ± T (mm)	500 ± 5	1000 ± 10	2000 ± 20
Farnell NO.	8706735	8706743	8706751
L ± T (mm)	3000 ± 30	5000 ± 40	10000 ± 70



SIDE: B

NOTE:

- (1). Cable Wiring: CAT. 5E UTP Stranded 24AWG(7*0.18CU)*4P
Jacket Material:LSOH OD:5.0 ± 0.20mm
- Cable Colour:BLUE
- Cable Printing: System Cable UTP CAT 5E 4 Pairs 24AWG
Stranded ISO 11801 100MHZ
- (2). Connector A&B: RJ45(8P8C) Male Type
INSULATION:Clear Polyester
- CONTACTS:Brass,Gold Plated
- (3). Over Mold: PVC, BLUE
- (4). Parameter Settings: UT8080M
- 1. Conductive Resistance:1kΩ
- 2. Insulative Resistance:5MΩ (Min.)
- (5). Packing: POLYBAG PACKING



PIN OUT: (4)

PACKING: (5)

GENERAL TOLERANCES
(UNLESS SPECIFIED)

Pro-SIGNAL

LENGTH: X, ± 1
.X ± 0.2
.XX ± 0.10
ANGLE: X°, ± 1°
.X° ± 0° 30'

UNIT: mm	REV: 0/A			NAME	CAT. 5E UTP CABLE(24AWG CD)
DRAWING	OVF	2011/12/20	S. P. NO.		
CHECK			P. O. NO.		
APPROVE			SIZE	PAGE	1/1

REV	DESCRIPTION	DATE
0		2011/12/14