

List Price \$382.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.****Technical Characteristics**

Operating Temperature Range	-13 to 158 Degrees F
Number of Poles	3-Pole
Pilot Light	Orange LED (100/240VAC)
Ampere Rating	10A
Lock Method	Inserting Actuating Key
Actuator Type	Key
Height	4.47 Inches
Connection Type	(1) 0.5 Inch NPT (Conduit Entrance)
Enclosure Rating	NEMA 4/4X/12 - IP67
Contact Operation	Slow Break (Break before Make)
Approvals	UL Listed File Number: E164353 CCN NKCR - CSA Certified File Number: LR4408794 Class 3211 03 - CE Marked
Enclosure Type	Water tight, Dust tight and Corrosion resistant (Indoor/Outdoor)
Contact Configuration	1 N.O./2 N.C.
Depth	1.73 Inches
Enclosure Material	Metal
Orientation	Actuating Key: Field Selectable - Electromagnet: Via conduit entrance
Maximum Voltage Rating	300VAC
Terminal Type	Screw Clamp
Type	XCSC

**Shipping and Ordering**

Category	22411 - Limit Switches, Heavy Duty, IEC, Type XCKJ
Discount Schedule	T
GTIN	00785901681601
Package Quantity	1
Weight	0.01 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	N
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.