

## LOGO! Communication modules

### Overview

**Every LOGO! can now be connected to the AS-Interface system**



AS-Interface connection for LOGO!

Using the AS-Interface connection for LOGO!, an intelligent slave can be integrated in the AS-Interface system. With the modular interface it becomes possible to integrate the different basic units in the system according to their functionality. Similarly, functionalities can be quickly and easily adapted to new requirements by exchanging the basic unit.

The interface module provides four inputs and four outputs on the system. These I/Os do not actually exist in hardware terms, however, but are only virtually present through the interface on the bus.

### Selection and ordering data

Version	DT	Screw terminals	PU (UNIT, SET, M)	PS*	PG
		Order No.	Price per PU		
<b>AS-Interface connections for LOGO!</b>					
Four virtual digital inputs, four virtual digital outputs	A	<b>3RK1 400-0CE10-0AA2</b>	1	1 unit	42C

Accessories [see page 10/30](#).

# LOGO! Logic Modules

## Accessories

### Selection and ordering data

Version	DT	Order No.	Price per PU	PU (UNIT, SET, M)	PS*	PG
<b>LOGO! TD text displays</b>						
<b>LOGO! TD text displays</b> 4-line text display, can be connected to all LOGO! basic and pure versions as from -0BA6 upwards, incl. connection cable	A	<b>6ED1 055-4MH00-0BA0</b>		1	1 unit	200
<b>SIPLUS LOGO! TD text displays</b>						
<b>SIPLUS LOGO! TD text displays</b> (extended temperature range -10 ... +60 °C and medial loading) 4-line text display, can be connected to all LOGO! 0BA6 basic and pure versions, degree of protection IP65, incl. connection cable	D	<b>6AG1 055-4MH00-2BA0</b>		1	1 unit	470
<b>SIPLUS voltage reducers</b>						
<b>SIPLUS Upmiter voltage reducers</b> For safe operation at combustion engine batteries • 1,25 A • 2,5 A	D	<b>6AG1 053-1AA00-2AA0</b>		1	1 unit	470
	D	<b>6AG1 203-1AA00-2AA0</b>		1	1 unit	471
<b>LOGO! Manuals</b>						
<b>LOGO! Manuals</b> • German • English • French • Spanish • Italian • Chinese	X	<b>6ED1 050-1AA00-0AE8</b>		1	1 unit	200
	X	<b>6ED1 050-1AA00-0BE8</b>		1	1 unit	200
	X	<b>6ED1 050-1AA00-0CE8</b>		1	1 unit	200
	X	<b>6ED1 050-1AA00-0DE8</b>		1	1 unit	200
	X	<b>6ED1 050-1AA00-0EE8</b>		1	1 unit	200
	X	<b>6ED1 050-1AA00-0KE8</b>		1	1 unit	200
<b>LOGO! Cards (only -0BA6)</b>						
<b>LOGO! memory cards</b> Program module for copying, with know-how protection (as from -0BA4 upwards)	A	<b>6ED1 056-1DA00-0BA0</b>		1	1 unit	200
<b>LOGO! battery cards</b> Battery modules for buffering the integrated real-time clock (not LOGO! 24)	A	<b>6ED1 056-6XA00-0BA0</b>		1	1 unit	200
<b>LOGO! memory/battery cards</b> Combined program and battery modules, with know-how protection and buffering of the integrated real-time clock (not LOGO! 24)	A	<b>6ED1 056-7DA00-0BA0</b>		1	1 unit	200
<b>SIPLUS LOGO! PROM</b> Programming units for simultaneous duplication of program module contents on up to 8 program modules	D	<b>6AG1 057-1AA01-0BA6</b>		1	1 unit	470
<b>LOGO! cables</b>						
<b>LOGO! PC cables</b> For transferring programs between LOGO! up to -0BA6 and PC	A	<b>6ED1 057-1AA00-0BA0</b>		1	1 unit	200
<b>LOGO! USB PC cables</b> For transferring programs between LOGO! up to -0BA6 and the PC, incl. drivers on CD-ROM,	A	<b>6ED1 057-1AA01-0BA0</b>		1	1 unit	200
<b>LOGO! modem cables</b> Adapter cables for analog modem communication, for LOGO! 0BA6	A	<b>6ED1 057-1CA00-0BA0</b>		1	1 unit	200
<b>Front panel assembly kits</b>						
<b>Front panel assembly kits</b> • Width: 4 MW • Width: 4 MW, with pushbuttons • Width: 8 MW • Width: 8 MW, with pushbuttons	C	<b>6AG1 057-1AA00-0AA0</b>		1	1 unit	470
	D	<b>6AG1 057-1AA00-0AA3</b>		1	1 unit	470
	C	<b>6AG1 057-1AA00-0AA1</b>		1	1 unit	470
	D	<b>6AG1 057-1AA00-0AA2</b>		1	1 unit	470
<b>LOGO! Starter kits (-0BA6)</b>						
<b>LOGO! starter kits 12/24 V</b> Contains LOGO! 12/24 RC, LOGO! USB PC cable, LOGO! Soft Comfort V6, language-neutral	A	<b>6ED1 057-3BA00-0AA6</b>		1	1 unit	2SP
<b>LOGO! starter kits 230 V</b> Contains LOGO! 230 RC, LOGO! USB PC cable, LOGO! Soft Comfort V6, language-neutral	A	<b>6ED1 057-3BA02-0AA6</b>		1	1 unit	2SP
<b>LOGO! TD starter kits 12/24 V</b> Contains LOGO! 12/24 RCo, LOGO! TD, LOGO! USB PC cable, LOGO! Soft Comfort V6, language-neutral	A	<b>6ED1 057-3BA10-0AA6</b>		1	1 unit	2SP
<b>LOGO! starter kits (-0BA7)</b>						
<b>LOGO! starter kits 12/24 V</b> Contains LOGO! 12/24 RCE, LOGO! Soft Comfort V7, LOGO! Power 24 V, 1.3 A, Ethernet cable, WinCC Basic V11, language-neutral	A	<b>6ED1 057-3BA00-0AA7</b>		1	1 unit	2SP
<b>LOGO! starter kits 230 V</b> Contains LOGO! 230 RCE, LOGO! Soft Comfort V7, Ethernet cable, WinCC Basic V11, language-neutral	A	<b>6ED1 057-3BA02-0AA7</b>		1	1 unit	2SP