
Item no.: 280-568
Product description: ACTUATOR SUPPLY TERMINAL BLOCK VOLTAGE SUPPLY
FROM CONTROL PANEL SIDE WITH END PLATE for
pressure and thermo switches



Produkt kann von Bild abweichen / product may differ

Packing unit 20 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	20 A
Weight	9.745 g
Color	gray
Wiring type	Angled Type
No. of connection Points	1
No. of potentials	1
Height	55.5 mm
Height	2.19 in
Width	6 mm
Width	0.236 in
Depth	80 mm

Depth	3.15 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
280-568	BV	07436/C0			0,08-2,5
280-568	CSA	154112-1536071	300	15	28-12
280-568	UR	E45172	300	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected