




FRONT VIEW




TABLE


ITEM NO	L
3073-2S	2000mm±30mm
3073-3	3000mm±30mm
3073-5	5000mm±30mm
3073-10	10000mm±30mm
3073-15	15000mm±30mm
3073-20	20000mm±30mm



FRONT VIEW



1.CABLE:ND UL.,28AWG/7/0.127),TINNED AND STRANDED COPPER WIRE
 INSULATOR:PVC,IDD:0.85mm ,CABLING:6C+DRAIN WIRE
 SHIELD:AL/MY COVERAGE
 JACKET:PVC, COMPLIANCE ROHS,COLOR:BEIGE,D.D:5mm
 2.PCS CONNECTOR:MINI 6 PIN MALE SOLDER TYPE CONNECTOR
 INSULATOR:P.B.T+GLASS FIBER,COLOR:BLACK
 CONTACT:COPPER ALLOY NICKEL PLATED
 SHELL:BRASS,NICKEL PLATED
 3.PCS CONNECTOR:MINI 6 PIN FEMALE SOLDER TYPE CONNECTOR
 INSULATOR:P.B.T+GLASS FIBER,COLOR:BLACK
 CONTACT:COPPER ALLOY NICKEL PLATED
 SHELL:BRASS,NICKEL PLATED



HEAT SEALED

MADE IN CHINA

PIN OUT

MINI6PIN PLUG(P1)	WIRE	MINI6PIN JACK(J1)
1		1
2		2
3		3
4		4
5		5
6	SHELL DRAIN WIRE	6

6.ELECTRONIC TEST
 100% OPEN SHORT+MISS WIRE TEST

PART NO. SHEET NO. 1 THIRD ANGLE PROJECTION

TITLE: P/S2 6 PIN MALE TO P/S2 6 PIN FEMALE
 BEIGE COLOR

DWN NO. SCALE: N.T.S. DRAWN BY & DATE
 UNIT: A4 CHECKED BY & DATE
 IN CH APPROVED BY & DATE