


MOLD	INSIDE NO.	OUTSIDE NO.
DB9P M/F	960278	960278

機密等級: [] 機密 [] 機密 [] 一般文件



PIN OUT
(DB9M)J1 J2(DB9F)

1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9

- NOTES:
1. WIRE: 28AWG 9C+1 AL/MY OD=5.0MM
 2. CONN: J1-DB9P MALE MOLDED TYPE W/T/S
J2-DB9P FEMALE MOLDED TYPE W/T/S+NUTS
 3. SCREW: 4*30.5MM(#4-40 UNC)
 4. NUT: 4.75*6MM(#4-40 UNC)
 5. INSIDE&OUTSIDE: MOLDING
 6. JACKET & OUTSIDE MOLD PVC COLOR : IVORY
 7. LENGTH: SEE THE TABLE
 8. PACKING: W/CLEAR POLYBAG/W/MADE IN CHINA ELECTRICAL TEST:

- 1)100% OPEN SHORT TEST
- 2)INSULATOR RESISTANCE:1M Ω MIN

G.W. NO	CUS. NO.	LENGTH
HCB112A0000000000	10000MM±100MM	

1-0		MAR-29-2007	
REV	DESCRIPTION	DATE	ECN NO.

DWG NAME: IBM PC MONITOR EXT CABLE	
G. W. NO: SEE THE TABLE	CUS. ID:
CUS. NO:	DWG. NO: DB9 M-F-04

RoHS Compliant

SHEET: 1/1	TOLERANCE: .X ±0.40	UNIT: mm
	.XX	DRAW. BY:
SCALE: 1:1		CHECKED
		APPROVE