

0

a m

CDAST

O laun





Contents

PRODUCTS

LED HANDHELDS

| Technology | 6–10 |
|-----------------------------|-------|
| High Performance LED Lights | 11–13 |
| Professional Use LED Lights | 14–15 |
| Tactical Use LED Lights | 16 |
| General Use LED Lights | 17–20 |
| A-Series LED Lights | 21–22 |

HEADLAMPS

| Technology2 | 23–25 |
|----------------|-------|
| LED Headlamps2 | 26–27 |

EMERGENCY AREA LIGHTS

| Technology | |
|------------|--|
| EALs | |

KNIVES

| Technology | 32–35 |
|---------------------------------|-------|
| Rapid Response [®] | 36 |
| Double-Lock™ Knives | 37–39 |
| Liner-Lock® and Lockback Knives | 40–44 |
| LED Knives | 45–46 |
| Fixed Blade Knives | 47 |
| | |
| Swiss Army Style Knives | |

MULTI-TOOLS

| Technology | 52 |
|-------------|-------|
| Multi-Tools | 53–55 |

ACCESSORIES

Knife & Tool Sharpeners.....56

DISPLAYS

SPECS CHART

| LED Lights Specifications61 | -63 |
|---------------------------------|-----|
| Knives & Tools Specifications64 | -66 |



COAST Products is a 93-year-old, family-owned company that produces LED lights, knives, and multitools for work, recreation, and everyday use.

COAST produces innovative, technologically advanced products backed by a lifetime guarantee that makes the user's life safer, easier, and more enjoyable.



LIFETIME GUARANTEE: COAST Products guarantees this product to be free of defects in materials and workmanship for the life of the original purchaser. This guarantee does not cover normal wear and tear, nor damage resulting from misuse or neglect. If this product is defective, return it to us for repair or replacement, along with a check for \$5.00 shipping and handling. Guarantee does not include batteries.

David C. Brands—Owner, COAST Products



Quality in Action





I am currently stationed in Iraq at Joint Base Balad. I purchased one of your LED flashlights...and it has been an invaluable asset to me getting the job I do here done. Thank you for having such wonderful products for us in the military available for us to purchase here.

—Steven P.


Since 1995, COAST has provided over 500,000 lights, knives, and multi-tools to U.S. military installations all over the world.







LED Handheld Technology





Pure Beam[™] Focusing Optic System

Max-Beam[™] Fixed Optic Technology

The Maximum Amount of Light for Your Application

FLOOD BEAM • Larger light area

Superior beam consistency

BULLS-EYE SPOT[™] BEAM

- Longer beam distance
- More intense Bulls-Eye Spot[™] Beam
- More consistent halo
- More light area



FLOOD BEAM

for General Use

BULLS-EYE SPOT[™] BEAM

for Tactical & Professional Use

INSPECTION BEAM

for Up-Close & Inspection Use





Key Technologies



Fingertip Speed Focus Control[™] & Beam Lock[™]

Many of our High Performance lights feature a onehanded system for moving from a broad flood beam to a focused spot beam. A simple push forward or pull back with the thumb on the head of the light adjusts the beam to suit your application. Then simply twist to lock in exactly the beam you need.



Twist Focus System

Twist the head of the flashlight to move between a flood and a spot beam.



Quick-Cycle Switch System[™]

To activate the high-output setting from the OFF position, fully depress and release the switch one time. High output setting is the standard setting when a bright light is needed. To activate the 50% beam setting from the OFF position, fully depress and release the switch two times. 50% output is useful for reading, report writing, identification and personal inspections.

Some COAST lights also feature a strobe as the second part of the cycle. In this case, the light sequence is high, strobe, low.



Dual Color

COAST dual color lights have both clear, bright white LEDs and a red LED. The white LEDs are perfect for general use, while the red LED offers glare-free light. Because the red beam doesn't cause the pupils of the eye to constrict, it preserves night vision. This makes it useful for reading maps at night or for locating things outdoors or in a darkened room without the dazzling glare of a white light.



Glossary of LED Flashlight Icons

| FINGERTIP SPEED FOCUS™ | FINGERTIP SPEED FOCUS – BEAM LOCK [™] : Focusing system that allows you to adjust your light from flood to spot with just your fingertip. Lock the beam focus in any position you want. |
|--|--|
| 4 Colors 4 Power Switches | 4 COLORS, 4 POWER SWITCHES: Our 4-color system combines one white LED, one red LED, one blue LED, one green LED, each color controlled with its own switch. |
| MAX BEAM™ OPTIC | MAX BEAM [™] OPTIC – BULLS-EYE SPOT [™] : It produces our Bulls-Eye Spot [™] beam giving you a great focused spot, while producing an outer ring of flood light which allows you to see a broader area for added side vision. |
| MAX BEAM™ OPTIC | MAX-BEAM [™] OPTIC – WHITE FLOOD BEAM: Multiple LEDs project a wide, flood beam giving you the maximum amount of light with no dark spots. |
| MAX BEAM® OPTIC | MAX-BEAM [™] OPTIC – WHITE INSPECTION BEAM: Produces a tight inspec- tion beam, giving you the most useful light beam for short distance applica- tions. |
| PURE BEAM TM FOCUSING OPTIC | PURE BEAM™ FOCUSING OPTIC – FLOOD BEAM / BULLS-EYE SPOT™: Our patented focusing system that provides superior beam consistency from spot to flood, with no dark rings typically associated with focusing flashlights. |
| OUICK-CYCLE SWITCH™ High & Low | QUICK-CYCLE SWITCH – HIGH & LOW: Allows you to select between a high output or a low output setting so you can choose the right level for your application. |
| OUICK-CYCLE SWITCH™ High / Strobe / Low | QUICK-CYCLE SWITCH – HIGH, STROBE & LOW: Allows you to select be- tween a high output, strobe, or low output setting so you can choose the right level for your application. |
| Twist to Focus | TWIST TO FOCUS: Our twist focusing system |
| White Flood & Red Spot Beam | WHITE FLOOD AND RED SPOT BEAM: Our dual-color system combines five white LEDs with one red LED, each color controlled with its own switch. |
| White Flood & UV Spot Beam | WHITE FLOOD AND UV SPOT BEAM: Our dual-color system combines three white LEDs with three UV LEDs, each color controlled with its own switch. |



HIGH PERFORMANCE LED LIGHTS































• 3 AAA batteries (included)









2.75 in. length 4 AG13 batteries (included)

































• 4.02 in. length

• 1 AAA battery (included)

G15 Clam Pack Item# TT75331CP





3.70 in. length

• 1 AAA battery (included)











• 3.70 in. length

• 1 AAA battery (included)





















01.

30

WWW -



LED Headlamp Technology





Glossary of Headlamp Icons

| Minged beam adjustment | HINGED BEAM ADJUSTMENT: Allows you to adjust direction of light beam. |
|--|--|
| MAX BEAM TH OPTIC | MAX BEAM [™] OPTIC – BULLS-EYE SPOT [™] : It produces our Bulls-Eye Spot [™] beam giving you a great focused spot, while producing an outer ring of flood light which allows you to see a broader area for added side vision. |
| MAX BEAM TH OPTIC | MAX-BEAM [™] OPTIC – WHITE FLOOD BEAM: Multiple LEDs project a wide, flood beam giving you the maximum amount of light with no dark spots. |
| PURE BEAM ^{MM} FOCUSING OPTIC | PURE BEAM™ FOCUSING OPTIC – FLOOD BEAM / BULLS-EYE SPOT™: Our patented focusing system that provides superior beam consistency from spot to flood, with no dark rings typically associated with focusing flashlights. |
| VARIABLE LIGHT TECHNOLOGY** Dimming function controls light output | VARIABLE LIGHT TECHNOLOGY: Dimming function that allows you to adjust your light output to just the right level for your application. |
| White Flood & Red Spot Beam | WHITE FLOOD AND RED SPOT BEAM: Our dual-color system combines five white LEDs with one red LED, each color controlled with its own switch. |











3 AAA batteries (included)
Neoprene pouch included



inged beam a











HL3 **Clam Pack Item# TT7454CP** Box Item# 19350


















LED Emergency Area Light Technology



Lets You Choose the Right Light for Every Situation







EAL15 **Clam Pack Item# C7050CP**

60

LUMENS Light Outp

HOUR



COAST Smart Switch 5-light-mode control

- 7.50 in. height
- Uses 4 C batteries (not included)
- 3 levels of white light (high/medium/low) • 2 red modes
- (solid/flashing)











Solid Red


Energy Saving












Emergency Red: Constant and Flashing







Introducing COAST's New Patented Blade-Assist Line of Knives





S.A.T.™ Smooth Assist Technology

Smooth Assist Technology— Not Just FASTER...SMOOTHER

Our patented system not only asists the blade to open quickly but smoothly due to its *frictionreducing roller-bearing* design. When the spring moves the blade out of the handle, it rides on the roller bearing, allowing the blade to open smoothly and quickly—without requiring tremendous spring force. The roller bearing also reduces the spring load on all internal bladeassist components for a lifetime of reliable, smooth, and fast operation.



Max-Lock[™] Technology

MAX-LOCK™

Conveniently positioned on the side of the handle allowing easy access for your thumb to lock or unlock the safety. Move it forward to lock and back to unlock. This secondary lock can be engaged with the blade open or closed.

Double-Lock[™] Technology





DOUBLE-LOCK[™]

Look for our new Double-Lock[™] technology in our large Liner-Lock[®] knives. When pushed forward into its engaged position, it prevents the Liner-Lock[®] from moving out of its locked position.

Also included is a *tension-adjusting feature* so the user can adjust the detent force required to move the Double-Lock[™] forward to engagement and rearward to the off position.

The Double-Lock[™] system works well for any knife owner and when it is engaged, adds that extra margin of safety for those that use their knife in extremely rugged conditions. For fire & rescue, police, military or challenging situations faced by anyone, the Double-Lock[™] sets the new standard for extreme use, knife safety, and convenience.



Glossary of Knife Icons

| S.A.T. TM S.MOOTH ASSIST TECHNOLOGY | S.A.T. [™] SMOOTH ASSIST TECHNOLOGY: S.A.T. [™] uses its friction-reducing roller- bearing design to allow the blade to open quickly but smoothly while reducing spring load on all internal blade-assist components. When the spring moves the blade out of the handle, it rides on the roller bearing, allowing the blade to open smoothly and quickly—without requiring tremendous spring force. |
|--|---|
| MAX-LOCK" | MAX-LOCK[™]: The Max-Lock [™] is a safety button on the side of the knife's handle that can lock the blade in both the open and closed positions. |
| DOUBLE-LOCK" | DOUBLE-LOCK™: The Double-Lock [™] safety switch mechanism works in conjunction with a primary Liner-Lock [®] blade lock system to prevent its disengagement. This makes a Liner-Lock [®] doubly safe. |
| LINER-LOCK® | LINER-LOCK®: The Liner-Lock [®] locking mechanism is a portion of the blades handle-liner that moves from the side of the handle into position to block the blade from closing when the blade is opened. This steel portion of the liner must be pushed to the side before the blade can be closed. |
| LOCKBACK | LOCKBACK: The Lockback blade locking system is located in the top of the knife handle and locks the blade by dropping a locking-bar into a locking notch at the top back-end of the blade. |
| MIDLOCK | MIDLOCK: The Midlock blade locking system is located in the top of the knife handle and locks the blade by dropping into a locking notch at the top back-end of the blade. The lock release is located midpoint between the front and back of the handle. |
| FRAME-LOCK | FRAME-LOCK: The Frame-Lock blade locking mechanism is part of the knife's frame that moves from the side frame of the knife when the blade is opened to block the blade from closing. This steel component of the frame must be pushed to the side to allow the blade to close. |
| BUTTON-LOCK | BUTTON-LOCK: The Button-Lock is a Liner-Lock [®] release button located in the side of the knife's handle and when it is pushed it releases the Liner-Lock [®] mechanism allowing the blade to close. |





- Blade length: 3.90 in.
- Overall length open: 8.75 in.
- Weight: 4.80 oz.

MAX-LOCI

Black oxide coated

- Blade material: High-carbon stainless steel
- Handle material: Fiberglass-filled textured nylon

36









- Blade material: 7Cr17 stainless steel
- Handle material: Grip-enhanced aluminum frame with stainless steel Double-Lock[™] Liner-Lock[®]
- Drop-point blade with thumb perch
- Stainless steel fasteners
- Deep-carry pocket clip
- Blade length: 3.50 in.
- Length closed: 4.65 in.
- Overall length open: 8.00 in.
- Weight: 3.90 oz.





- Blade material: 7Cr17 stainless steel
- Handle material: Grip-enhanced aluminum frame with stainless steel Double-Lock[™] Liner-Lock[®]
- One-inch serrated blade segment
- Stainless steel fasteners
- Deep-carry 3-position pocket clip
- Blade length: 3.25 in.
- Length closed: 4.70 in.
- Overall length open: 8.12 in.
- Weight: 4.20 oz.



- Blade material: 7Cr17 stainless steel
- Handle material: Grip-textured aluminum frame with stainless steel Double-Lock™ Liner-Lock[®]
- One-inch serrated blade segment
- Seat belt cutter & glass breaker
- Deep-carry pocket clip
- Blade length: 3.25 in.
- Length closed: 4.87 in.
- Overall length open: 8.12 in.
- Weight: 4.20 oz.



- Blade material: 7Cr17 stainless steel
- Handle material: Grip-textured aluminum frame with stainless steel Double-Lock[™] Liner-Lock[®]
- Clothing removal/seat belt blade serration
- Seat belt cutter & glass breaker
- Deep-carry pocket clip
- Blade length: 3.25 in.
- Length closed: 4.87 in.
- Overall length open: 8.12 in.
- Weight: 4.20 oz.

1074



- Blade material: 7Cr17 stainless steel
- Handle material: Black aluminum frame with stainless steel Double-Lock[™] Liner-Lock[®]
- Ambidextrous thumb stud
- Stainless steel fasteners
- Deep-carry stainless steel pocket clip
- Blade length: 3.35 in.
- Length closed: 4.65 in.
- Overall length open: 8.00 in.
- Weight: 3.50 oz.



- Blade material: 7Cr17 stainless steel
- Handle material: G-10 with stainless steel frame & Double-Lock[™] Liner-Lock[®]
- Drop-point blade with thumb perch
- Stainless steel fasteners
- Ambidextrous thumb-stud
- Deep-carry 3-position pocket clip
- Blade length: 3.50 in.
- Length closed: 4.75 in.
- Overall length open: 8.25 in.
- Weight: 5.00 oz.



- Blade material: 7Cr17 stainless steel
- Handle material: G-10 with stainless steel frame & Double-Lock[™] Liner-Lock[®]
- Drop-point blade with thumb perch
- One-inch serrated blade segment
- Stainless steel fasteners
- Ambidextrous thumb-stud
- Deep-carry 3-position pocket clip
- Blade length: 3.50 in.
- Length closed: 4.75 in.
- Overall length open: 8.25 in.
- Weight: 5.00 oz.





- Blade material: 400-series stainless steel
- Handle material: Textured aluminum with stainless steel Lockback
- Ambidextrous nail-nick opening in blade
- Stainless steel fasteners
- Key-ring included
- Blade length: 2.00 in.
- Length closed: 2.12 in.
- Overall length open: 4.60 in.
- Weight: .70 oz.









- Blade material: 400-series stainless steel
- Handle material: Black stainless steel frame with stainless steel Liner-Lock®
- Ambidextrous thumb stud
- Stainless steel fasteners
- Stainless steel deep-carry pocket clip
- Blade length: 2.37 in.
- Length closed: 3.25 in.
- Overall length open: 5.75 in.
- Weight: 1.90 oz.



- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: G-10 with stainless steel frame & Liner-Lock[®]
- Drop-point blade with thumb perch
- Stainless steel fasteners
- Deep-carry pocket clip
- Blade length: 2.50 in.
- Length closed: 3.50 in.
- Overall length open: 5.87 in.
- Weight: 2.10 oz.




- Blade material: 400-series stainless steel
- Handle material: Black nylon with stainless steel Liner-Lock®
- Ambidextrous thumb stud
- Stainless steel fasteners
- Stainless steel deep-carry pocket clip
- Blade length: 3.25 in.
- Length closed: 4.12 in.
- Overall length open: 7.30 in.
- Weight: 1.90 oz.









- Handle material: Stainless frame &
- One-inch serrated blade segment
- Ambidextrous thumb stud
- Stainless steel fasteners & deep-carry
- Blade length: 2.75 in.
- Length closed: 4.12 in.
- Overall length open: 6.87 in.
- Weight: 4.20 oz.



- Blade material: 400-series stainless steel
- Handle material: Aluminum, with stainless steel Liner-Lock[®]
- One-inch serrated blade segment
- Ambidextrous thumb stud
 - Pocket clip for easy carry
 - Blade length: 2.875 in.
 - Length closed: 3.875 in.
 - Overall length open: 6.75 in.
 - Weight: 1.80 oz.





- Blade material: 400-series stainless steel
- Handle material: Stainless steel frame & Liner-Lock® with button release
- One-inch serrated blade segment
- Ambidextrous thumb stud
- Stainless steel fasteners
- Blade length: 2.75 in.
- Length closed: 3.75 in.
- Overall length open: 6.50 in.
- Weight: 2.60 oz.



- Blade material: 400-series stainless steel
- Handle material: Checkered aluminum with stainless steel Liner-Lock®
- One-inch serrated blade segment
- Ambidextrous blade opening
- Stainless steel fasteners & deep-carry pocket clip
- Blade length: 3.00 in.
- Length closed: 4.00 in.
- Overall length open: 7.00 in.
- Weight: 2.50 oz.





- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: Black checkered aluminum
- Stainless steel Liner-Lock®
- Stainless steel fasteners
- Stainless steel deep-carry pocket clip
- Blade length: 3.00 in.
- Length closed: 4.25 in.
- Overall length open: 7.25 in.
- Weight: 2.70 oz.



- Blade material: 7Cr17 high-carbon stainless steel
- Stainless steel frame
- Handle material: Contoured & stabilized wood
- Frame-Lock safety
- Ambidextrous thumb stud
- Max-Grip handle design
- Blade length: 4.00 in.
- Length closed: 4.87 in.
- Overall length open: 8.75 in.
- Weight: 5.10 oz.





- LOCKBACK KNIFE 🔌
- Blade material: 7Cr17 high-carbon stainless steel
- Handle material: Checkered G10 handle/frame with stainless steel Lockback
- Thumb perch for secure grip
- One-inch serrated segment on blade
- Stainless steel fasteners
- Stainless steel pocket clip
- Blade length: 3.25 in.
- Length closed: 4.12 in.
- Overall length open: 7.87 in.
- Weight: 3.10 oz.






- Blade material: 400-series stainless steel
- Handle material: Nylon
- LED light
- Bottle opener
- Stainless steel frame
- Liner-Lock[®]
- Large nail nick for one-handed opening
- Hole for key-ring attachment
- Blade length: 1.12 in.
- Length closed: 3.00 in.
- Overall length open: 4.00 in.
- Weight: 1.20 oz.











Hardwood Hunter

Clam Pack Item# C652CP



- Blade material: 400-series stainless steel
- Handle material: Natural Stag
- Traditional styling
- Brass handle rivets
- Quality leather sheath
- Lanyard hole
- Blade length: 3.75 in.
- Blade thickness: .112 in.
- Overall length: 7.50 in.
- Weight: 5.10 oz. (with sheath)
- Blade material: 400-series stainless steel
- Handle material: Laminated & stabilized wood
- Traditional styling
- Brass handle rivets
- Quality leather sheath
- Lanyard hole
- Blade length: 3.75 in.
- Blade thickness: .112 in.
- Overall length: 7.00 in.
- Weight: 5.10 oz. (with sheath)



- Blade material: 9Cr18 Mov high-carbon stainless steel
- Handle material: Textured elastomer
- Blade-back saw
- Full-tang construction with threaded slainless steel butt-cap and striker
- Molded nylon sheath
- Lanyard hole
- Blade length: 6.00 in.
- Blade thickness: .156 in.
- Overall length: 11 in.
- Weight: 10.80 oz. (with sheath)



Metal Commander

Clam Pack Item# C5017CP



- Blade material: Stainless steel blade and tools
- Handle material: Textured aluminum
- Includes knife blade, file, mini screwdriver tip, springless scissors
- Blade length: 1.50 in.
- Length closed: 2.25 in.
- Overall length open: 3.75 in.
- Weight: .50 oz.



- Blade material: Stainless steel blades and tools
- Handle material: Textured aluminum
- Includes large knife blade, small knife blade, bottle opener, can opener, wire stripper, hole punch, slotted screwdriver tip, small slotted screwdriver tip, Phillips screwdriver tip, key ring
- Blade length: 2.50 in. main
- Length closed: 3.5 in.
- Overall length open: 6.25 in.
- Weight: 2.00 oz.



- Blade material: Stainless steel blades and tools
- Handle material: Textured aluminum
- Includes large knife blade, small knife blade, scissors, bottle opener, can opener, wire stripper, hole punch, slotted screwdriver tip, small slotted screwdriver tip, saw blade, Phillips screwdriver tip, key ring
- Blade length: 2.50 in. main
- Length closed: 3.5 in.
- Overall length open: 6.25 in.
- Weight: 3.50 oz.



7-inch Fillet Knife Clam Pack Item# C846CP



- Blade material: Flexible stainless steel
- Handle material: Elastomer sure-grip for comfort
- Serrated segment for rugged cutting
- Lanyard hole
- Molded hard protective sheath
- Blade length: 7.00 in.
- Overall length: 12.50 in.
- Weight: 5.20 oz.



Folding Fillet Knife

Clam Pack Item# C899CP

Folding Fish Tool

& 12-Piece Bit Set

Clam Pack Item# FT8500CP



0)(

- Blade material: Flexible stainless steel
- Handle material: Tough & easy-to-clean nylon
- Lock-back locking system
- Stainless steel rivets
- 8-inch lanyard included
- Blade length: 7.00 in.
- Length closed: 7.12 in.
- Overall length open: 13.00 in.
- Weight: 2.80 oz.

- 100% stainless steel construction
- Includes: marlin spike, scissors, wire cutter, long-reach needle nose pliers with crimpers for leaders, stops and sleeves. Main blade with serration, Phillips head screwdriver, bottle opener, flat blade screwdriver, and bit driver.
- Locking blades and components
- Nylon sheath
- 32-piece bit set: 3 slotted, 3 Phillips, 6 hex head
















6

6

0




2-LED Pro Pocket Pliers[™] Clam Pack Item# C5899CP Box Item# C5899

2-LED Pro Pocket Pliers[™] Black Clam Pack Item# C5899BCP Box Item# C5899B

2 built-in LEDs, 9 functions

- One LED in front, one in rear, click to choose
- Blade material: 400-series stainless steel
- Spring-loaded pliers head
- Sure grip handle inlays
- 3-inch, easy-open knife blade, partial serration
- Scissors, screwdrivers, cap lifter, more
- LED runtime 10-15 hours
- 4 in. closed
- Includes semi-rigid sheath
- Weight: 9.80 oz.








Micro Toolbox[™] Clam Pack Item# C3700CP



- · Bead-blasted stainless steel
- Includes 3 wrenches, bottle opener, knife blade with partial serration, file blade, nail pick, springless Lever Action scissors, Phillips screwdriver, saw blade, large and small screwdrivers, ruler
- 2.50 in. closed
- Key ring
- Weight: 1.40 oz.







- Bead-blasted stainless steel
- Includes 4 wrenches, bottle opener, knife blade with partial serration, file, slip-joint pliers, Phillips screwdriver, large and small screwdrivers, ruler
- 3.75 in. closed
- Lanyard
- Weight: 2.80 oz.



Pocket-sized Micro Pliers[™] have built-in LED light

- Built-in LED light: click for constant on
- 400-series stainless steel
- Sure grip handle inlays
- Spring loaded pliers head for easy one-handed operation
- Includes LED light in handle, pliers, wire cutter, main knife blade, saw blade, keyring, Phillips screwdriver, bottle opener with flathead screwdriver tip and wire stripper, awl, file with nail pick, can opener with small flathead screwdriver tip
- Light takes two (2) CR927 batteries
- 3 in. closed







Diamond Sharpener Large Item# CM-1

- Diamond-particle coated shaft
- Sharpens knives, tools, scissors, fish hooks—almost anything metal!
- Pocket clip
- Weight: 1.40 oz.
- Overall length: 5.50 in.
- Diamond sharpening surface: 2.50 in.

Diamond Sharpener Medium Item# CM-2



- Diamond-particle coated shaft
- Sharpens knives, tools, scissors, fish hooks—almost anything metal!
- Pocket clip
- Weight: .60 oz.
- Overall length: 3.75 in.
- Diamond sharpening surface: 2.25 in.

Pocket Sharpening Stone Item# 19413



- Sharpens quickly and easily
- Designed for sharpening everything from pocket knives to tools and shears
- Leather sheath
- Length: 2.00 in.



Please contact your sales administrator for display assortment information and pricing.

LED Multi-Tool Quarter Pallet Display 35.5" H x 18.5" W x 21.875" D



G25 Quarter Pallet Display 35.5" H x 18.5" W x 21.875" D



LED Headlamp Quarter Pallet Display 35.5" H x 18.5" W x 21.875" D



Emergency Area Light Quarter Pallet Display 47.5" H x 22.625" W x 22.5" D





G40/G35 Quarter Pallet Display 49" H x 2" W x 20" D



Power Panel

48" H x 15" W x 16.5" D (Base) 48" H x 15" W x 4.5" D (Display)



2-Sided Display 71" H x 25.75" W x 24.5" D





Free-Standing Sidekick Display 45" H x 21" W x 16.625" D



Rolling Display Cabinet with Spinner

45" H x 20.125" W x 8.75" D (Rolling Display) 24" H x 15" W x 4.5" D (Spinner)



Dumpbin Box

40" H x 16.375" W x 18.375" D





LED Flashlight Header Sign 12.25" H x 46" W x 25" D



Available for Sporting Goods & Hardware channels



Acrylic Flashlight Stand 2.875" H x 6" W x 2.375" D



Knife Counter Display 9" H x 11" W x 5.75" D



Folding Acrylic Knife/Flashlight Stand

Large: 1.5" H x 5" W x 2" D Small: 1.25" H x 3.75" W x 2" D





| MODEL IMAGE | PRODUCT NAME | ITEM# Clam Pack / Box | BATTERY TYPE | MAX. LUMENS | RUN TIME | BEAM DIST. | OVERALL Size (in.) | WEIGHT (INCL. BATTERIES) | PAGE # |
|----------------|--------------|-----------------------------|-----------------|----------------|-------------|---------------|-----------------------|--------------------------------|-----------|
| au) | A25 | 19247 | 4 x AAA | 226 | 5 h | 205 m | 5.50 | 10.4 oz | 21 |
| () Carr | A20 | 19267 | 3 x AAA | 171 | 6 h 15 min | 64 m | 3.67 | 4.4 oz | 21 |
| Car | A15 | 19266 | 3 x AAA | 194 | 3 h 45 min | 127 m | 3.90 | 5 oz | 21 |
| 0 | A9 | 19364 / 19335 | 3 x AAAA | 20 | | | 7.03 | | 22 |
| 0 | A10 | 19246 | 2 x AAA | 66 | 1 h 30 min | 70 m | 5.48 | 3.2 oz | 22 |
| | A5 | 19245 | 1 x AAA | 26 | 7 h 15 min | 20 m | 3.74 | 2 oz | 22 |
| | EAL20 | CE7124HGB | 4 x D | 375 | 100 h | N/A | 8.25 | 32.02 oz | 30 |
| | EAL15 | C7050CP | 4 x C | 60 | 50 h | N/A | 7.50 | 16.06 oz | 30 |
| | EAL10 | C7040CP | 4 x AA | 17 | 30 h | N/A | 5.75 | 9 oz | 31 |
| | EAL5 | C7044CP | 4 x AAA | 15 | 40 h | N/A | 5.375 | 4.6 oz | 31 |
| 10 | G50 | TT8607CP / 19299 | 3 x AAA | 166 | 7 h | 143 m | 4.80 | 5.8 oz | 17 |
| | G45 Black | 19300 / 19356 | 3 x AAA | 135 | 8 h 30 min | 53 m | 4.60 | 3.6 oz | 17 |
| ()) - | G45 Titanium | TT7345SCP | 3 x AAA | 135 | 8 h 30 min | 53 m | 4.60 | 3.6 oz | 17 |
| | G40 | TT1006CP | 3 x AAA | 130 | 11 h | 52 m | 6.03 | 5 oz | 18 |
| | G35 | TT1106CP | 3 x AAA | 111 | 10 h 15 min | 47 m | 6.03 | 5.2 oz | 18 |
| Contraction | G30 | TT8606CP / 19298 | 2 x AA | 121 | 2 h | 146 m | 6.46 | 5.6 oz | 17 |



| MODEL IMAGE | PRODUCT NAME | ITEM# Clam Pack / Box | BATTERY TYPE | MAX. LUMENS | RUN TIME | BEAM DIST. | OVERALL Size (in.) | WEIGHT (INCL. BATTERIES) | PAGE # |
|--|--------------|-----------------------------|------------------------------|----------------|-------------|---------------|-----------------------|--------------------------------|-----------|
| t court | G25 Black | TT7547BLCP / 19355 | 2 x AA | 83 | 9 h 45 min | 41 m | 6.05 | 3.6 oz | 18 |
| aur F | G25 Titanium | TT7547CP | 2 x AA | 83 | 9 h 45 min | 41 m | 6.05 | 3.6 oz | 18 |
| and the second | G20 | TT7817CP / 19304 | 2 x AAA | 36 | 12 h 15 min | 22 m | 5.65 | 2.4 oz | 19 |
| Come Canada | G19 | 19384 | 1 x AAA | | | | 4.02 | | 19 |
| 7 | G15 | TT75331CP | 1 x AAA | 32 | 2 h 45 min | 24 m | 3.70 | 1.5 oz | 19 |
| (and the second se | G10 Black | TT7830CP | 1 x AAA | 32 | 2 h 45 min | 24 m | 3.70 | 1.2 oz | 20 |
| 0 | G10 Titanium | TT7831CP | 1 x AAA | 32 | 2 h 45 min | 24 m | 3.70 | 1.2 oz | 20 |
| and the second | G5 | TT7839CP | 4 x AG5 | 33 | 45 min | 24 m | 2.45 | .4 oz | 20 |
| | HL7 | 19284 / 19273 | 3 x AAA | 196 | 5 h 45 min | 109 m | N/A | 4.4 oz | 26 |
| | HL7R | TT7498CP / 19274 | 3 Ni-MH Recharge- able | 150 | 3 h | 114 | N/A | 4.4 oz | 26 |
| | HL6 | TT7468CP / 19268 | 3 x AAA | 181 | 6 h 15 min | 111 m | N/A | 4.2 oz | 26 |
| A | HL5 | TT7041CP / 19351 | 3 x AAA | 175 | 3 h 45 min | 56 m | N/A | 4.4 oz | 27 |
| | HL4 | 19291 | 3 x AAA | 144 | 6 h 15 min | 57 m | N/A | 4.4 oz | 27 |
| E | HL3 | TT7454CP / 19350 | 3 x AAA | 60 | 12 h 30 min | 43 m | N/A | 4.4 oz | 27 |
| | HP21 | 19282 | 4 x D | 1317 | 2 h 15 min | 260 m | 15.50 | 2.8 lbs | 11 |
| | HP21R | 19390 | Ni-MH Recharge- able | | | | 15.50 | 2.8 lbs. | 11 |



| MODEL IMAGE | PRODUCT NAME | ITEM# Clam Pack / Box | BATTERY TYPE | MAX. LUMENS | RUN TIME | BEAM DIST. | OVERALL SIZE (IN.) | WEIGHT (INCL. BATTERIES) | PAGE # |
|--|--------------|-----------------------------|-----------------|----------------|-------------|---------------|-----------------------|--------------------------------|-----------|
| Contraction of the second | HP17 | HP8417CP | 3 x D | 615 | 15 h 15 min | 269 m | 13.12 | 1.9 lb | 11 |
| | HP17TAC | 19281 | 3 x D | 615 | 15 h 15 min | 269 m | 13.12 | 1.9 lb | 13 |
| | HP14 | HP8414CP / 19280 | 4 x AA | 339 | 4 h 45 min | 175 m | 8.38 | 14.2 oz | 11 |
| Contraction of the second seco | HP7 | HP8407CP / 19279 | 4 x AAA | 251 | 5 h 45 min | 196 m | 5.58 | 7.2 oz | 12 |
| C | HP7 Titanium | HP8420-TCP-P3 / 19235 | 4 x AAA | 251 | 5 h 45 min | 196 m | 5.58 | 7.2 oz | 12 |
| 6 | HP7TAC | HP8407AFCP | 4 x AAA | 251 | 5 h 45 min | 196 m | 5.58 | 7.2 oz | 13 |
| Galera | HP6 | HP8406CP / 19278 | 2 x AA | 170 | 5 h | 104 m | 6.62 | 4.6 oz | 12 |
| 0 | HP6TAC | HP8406AFCP | 2 x AA | 170 | 5 h | 104 m | 6.62 | 4.6 oz | 13 |
| C. J. C. | HP5 | HP8405CP / 19277 | 1 x AA | 121 | 4 h 30 min | 78 m | 4.65 | 3 oz | 12 |
| C | HP5TAC | HP8405AFCP | 1 x AA | 121 | 4 h 30 min | 78 m | 4.65 | 3 oz | 13 |
| 1 martin | HP4 | HP8404CP / 19276 | 2 x AAA | 95 | 4 h 15 min | 57 m | 5.54 | 2.2 oz | 12 |
| (F as see | PX50 | TT7456CP | 4 x AA | 131 | 9 h 15 min | 195 m | 6.50 | 8.4 oz | 14 |
| | PX45 | 19285 / 19265 | 3 x AAA | 212 | 7 h 15 min | 186 m | 5.20 | 5.8 oz | 14 |
| 00000 | РХ25 | TT7736CP / 19270 | 3 x AAA | 208 | 6 h 15 min | 128 m | 4.70 | 4.2 oz | 14 |
| | PX20 | 19286 / 19271 | 3 x AAA | 125 | 5 h 30 min | 53 m | 3.95 | 3.2 oz | 15 |
| | PX10 | 19269 | 3 x AAA | 59 | 14 h | 39 m | 3.95 | 3 oz | 15 |
| () () | РХ5 | HP8313CP / 19275 | 4 x AG13 | 44 | 1 h 45 min | 21 m | 2.75 | 1.2 oz | 15 |
| 0 | TX40 | TT7736TSCP / 19272 | 3 x AAA | 164 | 7 h 45 min | 158 m | 5.94 | 5.4 oz | 16 |
| | TX10 | TT77364CP | 3 x AAA | 73 | 8 h 15 min | 36 m | 3.95 | 3 oz | 16 |



| MODEL IMAGE | PRODUCT NAME | ITEM# Clam Pack / Box | BLADE Size (in.) | OVERALL SIZE (IN.) | WEIGHT (OZ.) | LOCK System | BLADE MATERIAL | HANDLE Material | PAGE # |
|--|----------------------------|-----------------------------|------------------------|-----------------------|-------------------|---|-------------------------------|---------------------------|-----------|
| | 3-in-1 Tool | C53BCP | 1.12 | 4.00 | 1.20 | Liner-Lock® | 400-series stainless steel | Nylon | 45 |
| | 3-in-1 Tool | C53RCP | 1.12 | 4.00 | 1.20 | Liner-Lock [®] | 400-series stainless steel | Nylon | 45 |
| | 7-Inch Fillet Knife | C846CP | 7.00 | 12.50 | 5.20 | N/A | Stainless steel | Kraton® | 49 |
| | 9-Inch Fillet Knife | C849CP | 9.00 | 14.50 | 5.80 | N/A | Stainless steel | Kraton® | 49 |
| - Marine Contraction of the Cont | Adventurer | C5034CP | 2.5 main/ 1.5 small | 6.25 | 2.00 | N/A | Stainless steel | Textured aluminum | 48 |
| | Black Magic Liner-Lock® | CG006CP / CG006 | 3.35 | 7.75 | 3.20 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Checkered aluminum | 37 |
| | Button-Lock Folder | C05CP / C05 | 2.75 | 6.50 | 2.60 | Liner-Lock [®] | 400-series stainless steel | Stainless steel | 43 |
| | Button-Lock Black | CO3BCP / CO3B | 2.75 | 6.50 | 2.60 | Liner-Lock [®] | 400-series stainless steel | Stainless steel | 43 |
| (100 P.). | Compact Tactical | C20146PLCP / C20146 | 2.37 | 5.75 | 1.90 | Liner-Lock [®] | 400-series stainless steel | Black stainless steel | 41 |
| | Dark Force I | 19339 / 19340 | 3.50 | 8.25 | 5.00 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Grip-enhanced G-10 | 39 |
| | Dark Force II | 19357 / 19358 | 3.50 | 8.25 | 5.00 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Grip-enhanced G-10 | 39 |
| | Folding Fillet Knife | C899CP | 7.00 | 13.00 | 2.80 | Lockback | Stainless steel | Nylon | 50 |
| | Ghost I | 19311 / 19312 | 3.25 | 7.87 | 3.80 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Grip-enhanced aluminum | 39 |
| | Ghost II | 19313 / 19314 | 3.50 | 8.00 | 3.70 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Grip-enhanced aluminum | 39 |
| | H.A.R.D. Field Knife | C1104CP / C1104 | 4.00 | 8.75 | 5.10 | Frame-Lock | 7Cr17 | Wood | 44 |
| | Hardwood Hunter | C652CP | 3.75 | 7.00 | 5.10 in sheath | N/A | 400-series stainless steel | Hardwood | 47 |
| | Key-Ring Lockback | CG002PLCP / CG002PL | 2.00 | 4.60 | 0.70 | Lockback | 400-series stainless steel | Textured aluminum | 40 |
| | Key-Ring Lockback | CG002BHCP / CG002BH | 2.00 | 4.60 | 0.70 | Lockback | 400-series stainless steel | Textured aluminum | 40 |
| | LED Compact Knife | C7401CP | 2.50 | 6.50 | 2.70 | Liner-Lock [®] | 400-series stainless steel | Rubberized handle | 45 |
| | LED Compact Knife Black | 19248 | 2.50 | 6.50 | 2.70 | Liner-Lock [®] | 400-series stainless steel | Rubberized handle | 45 |
| | LED Liner-Lock® | C7400CP | 3.375 | 8.25 | 5.10 | Liner-Lock [®] | 400-series stainless steel | Rubberized handle | 46 |
| Contraction of the second seco | LED Pocket Tool | 19344 | 3.00 | 7.12 | 4.60 | Liner-Lock® | 400-series stainless steel | Stainless steel frame | 46 |
| | LED Pocket Tool Black | 19346 | 3.00 | 7.12 | 4.60 | Liner-Lock® | 400-series stainless steel | Stainless steel frame | 46 |
| 4 | Metal Commander | C5017CP | 1.50 | 3.75 | 0.50 | N/A | Stainless steel | Textured aluminum | 48 |



| MODEL IMAGE | PRODUCT NAME | ITEM# Clam Pack / Box | BLADE Size (in.) | OVERALL SIZE (IN.) | WEIGHT (OZ.) | LOCK System | BLADE MATERIAL | HANDLE MATERIAL | PAGE # |
|--|---|-----------------------------|------------------------|-----------------------|-------------------|---|--------------------------------|----------------------------------|-----------|
| | Mini-Tac | 19341 / 19342 | 2.50 | 5.87 | 2.10 | Liner-Lock® | 7Cr17 | G-10 with stainless steel frame | 41 |
| | Mini-Tac | 19337 / 19338 | 2.50 | 5.87 | 2.10 | Liner-Lock [®] | 7Cr17 | G-10 with stainless steel frame | 41 |
| | Natural Stag- Bone Hunter | C8520SBCP | 3.75 | 7.50 | 5.10 in sheath | N/A | 400-series stainless steel | Stag | 47 |
| | P.D.T. Police Duty Tactical | 19305 / 19306 | 3.25 | 8.12 | 4.20 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Grip-enhanced aluminum | 38 |
| 0 p * 0((a)*** | Pro Predator Lockback | 19325 / 19326 | 3.25 | 7.87 | 3.10 | Lockback | 7Cr17 | Checkered G-10 | 44 |
| and the second sec | Rapid Response® 3.90 | 19213 / 19393 | 3.90 | 8.75 | 4.80 | Liner-Lock [®] + Max-Lock [™] | High-carbon stainless steel | Fiberglass-filled textured nylon | 36 |
| 0.14 | Rapid Response [®] 3.90 Black | 19214 / 19394 | 3.90 | 8.75 | 4.80 | Liner-Lock [®] + Max-Lock [™] | High-carbon stainless steel | Fiberglass-filled textured nylon | 36 |
| | Rapid Response® 3.00 | 19211 / 19391 | 3.00 | 7.00 | 3.70 | Liner-Lock [®] + Max-Lock™ | High-carbon stainless steel | Fiberglass-filled textured nylon | 36 |
| 5.7 | Rapid Response® 3.00 Black | 19212 / 19392 | 3.00 | 7.00 | 3.70 | Liner-Lock [®] + Max-Lock [™] | High-carbon stainless steel | Fiberglass-filled textured nylon | 36 |
| | Raptor Tactical/ Field Knife | CUS100CP | 6.00 | 11.00 | 10.80 in sheath | N/A | High-carbon stainless steel | Textured Elastomer | 47 |
| | Repairman | C5037CP | 2.5 main/ 1.5 small | 6.25 | 3.50 | N/A | Stainless steel | Textured aluminum | 48 |
| | R.T.OI Rescue Team Operator | 19307 / 19308 | 3.25 | 8.12 | 4.20 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Grip-textured aluminum | 38 |
| | R.T.OII Rescue Team Operator | 19309 / 19310 | 3.25 | 8.12 | 4.20 | Liner-Lock [®] + Double-Lock [™] | 7Cr17 | Grip-textured aluminum | 38 |
| C. 0000000 | Skeleton Folder | C07CP / C07 | 2.75 | 6.87 | 4.20 | Liner-Lock [®] | 7Cr17 | Brushed stainless steel | 42 |
| | Skeleton Folder Black | C07BCP / C07B | 2.75 | 6.87 | 4.20 | Liner-Lock [®] | 7Cr17 | Black stainless steel | 42 |
| | S.P.T. | C08CP / C08 | 3.00 | 7.25 | 2.70 | Liner-Lock [®] | 7Cr17 | Black checkered aluminum | 44 |
| | Tactical Liner-Lock® | C19CP / C19 | 3.35 | 8.00 | 3.50 | Liner-Lock® + Double-Lock™ | 7Cr17 | Black aluminum | 38 |
| | Talon Folder | C36CP / C36 | 3.25 | 7.30 | 1.90 | Liner-Lock® | 400-series stainless steel | Contoured checkered nylon | 41 |
| | Tuff-Task | CG004PLCP / CG004PL | 3.00 | 7.00 | 2.50 | Liner-Lock® | 400-series stainless steel | Black checkered aluminum | 43 |
| | Tuff-Task Black | CG004BHCP / CG004BH | 3.00 | 7.00 | 2.50 | Liner-Lock® | 400-series stainless steel | Black checkered aluminum | 43 |
| | X-Frame Folder | C20136PLCP / C20136PL | 2.50 | 5.75 | 3.00 | Liner-Lock® | 400-series stainless steel | Stainless steel | 42 |
| | X-Frame Folder Black | C20136MBCP / C20136MB | 2.50 | 5.75 | 3.00 | Liner-Lock® | 400-series stainless steel | Stainless steel | 42 |
| | X-Frame Liner-Lock® | C008CP / C008 | 2.87 | 6.75 | 1.80 | Liner-Lock® | 400-series stainless steel | Aluminum | 42 |
| | Z-Frame Large | C22CP / C22 | 2.50 | 6.12 | 3.80 | Liner-Lock® | 7Cr17 | Brushed stainless steel | 40 |
| | Z-Frame Large Black | C22BCP / C22B | 2.50 | 6.12 | 3.80 | Liner-Lock® | 7Cr17 | Black stainless steel | 40 |
| | Z-Frame Small | C21CP / C21 | 1.75 | 4.37 | 1.40 | Liner-Lock [®] | 400-series stainless steel | Stainless steel | 40 |



| MODEL IMAGE | PRODUCT NAME | ITEM# Clam Pack / Box | BLADE Size (in.) | OVERALL SIZE (IN.) | WEIGHT (OZ.) | LOCK System | BLADE MATERIAL | HANDLE MATERIAL | PAGE # |
|--|---|-----------------------------|----------------------------|-----------------------|--------------------------|----------------|------------------------------------|-----------------------------|-----------|
| - Contraction of the second | 2-LED Pro Pocket Pliers | C5899CP / C5899 | 3.25 | 7.25 | 9.80 | Liner-Lock® | 400-series stainless steel | Stainless steel / rubber | 53 |
| - | 2-LED Pro Pocket Pliers Black | C5899BCP / C5899B | 3.25 | 7.25 | 9.80 | Liner-Lock® | 400-series stainless steel | Stainless steel / rubber | 53 |
| | 7-Inch Pro Fishing Pliers | FT6500CP | N/A | 7.00 | 6.20 | N/A | Titanium-coated stainless steel | Rubberized handle | 51 |
| × | 9-Inch Pro Fishing Pliers | FTP8000CP | N/A | 9.00 | 7.60 | N/A | Titanium-coated stainless steel | Rubberized handle | 51 |
| | Folding Fish Tool & 12-Piece Bit Set | FT8500CP | 3.25 | 8.00 | 13.60 | N/A | Stainless steel | Bead blasted / rubber | 50 |
| A Company of the second | LED Micro Pliers | C2899CP / C2899 | 2.25 | 4.50 | 4.40 | N/A | 400-series stainless steel | Stainless / rubber | 55 |
| | LED Micro Pliers Black | C2899BCP / C2899B | 2.25 | 4.50 | 4.40 | N/A | 400-series stainless steel | Stainless / rubber | 55 |
| | LED Pocket Pliers | C5799CP / C5799 | 2.00 | 6.00 | 11.80 | N/A | 400-series stainless steel | Stainless / rubber | 54 |
| | LED Pocket Pliers Black | C5799BCP / C5799B | 2.00 | 6.00 | 11.80 | N/A | 400-series stainless steel | Stainless / rubber | 54 |
| ő | Micro Fishing Tool | MP2875CP | 1.50 | 4.50 | 2.60 | N/A | 400-series stainless steel | Bead-blasted | 51 |
| | Micro Toolbox | C3700CP | 1.75 | 4.00 | 1.40 | N/A | stainless steel | Bead-blasted | 54 |
| | Pocket Toolbox | C3900CP | 2.50 | 6.00 | 2.80 | N/A | stainless steel | Bead-blasted | 55 |
| | Titanium Split- Ring Pliers | FT2401CP | N/A | 5.00 | 3.20 | N/A | Titanium-coated steel | ABS | 51 |
| | Diamond Sharpener Large | CM-1 | 2.50 diamond surface | 5.50 | 1.40 | N/A | N/A | Aluminum | 56 |
| | Diamond Sharpener Medium | CM-2 | 2.25 diamond surface | 3.75 | .60 | N/A | N/A | Aluminum | 56 |
| _ | Pocket Sharpening Stone | 19413 | N/A | 2.00 | N/A | N/A | N/A | N/A | 56 |



P.O. Box 5821 • Portland, OR 97228 503-234-4545 • Fax 503-234-4422 Toll Free 1-800-426-5858 www.COASTportland.com



