



Deutsche Version

- Home
- About Us
- Products**
  - Audio**
  - Video
  - Lighting
  - Data Connectors
  - Industrial

- Support
- News
- Sitemap

Search

PRODUCTS ONLY

Search

© Neutrik® AG  
 All rights reserved  
 Legal Notices



Audio

## 1/4" Prof. Phone Plugs, X-Series

[back](#)

### NP3RX

#### Product

Connector Type	Plug
Gender	male

#### Electrical

Contact resistance	depends on mating connector mΩ
Dielectric strength	1 kVdc
Insulation resistance	> 2 GΩ (initial)
Insulation resistance	≥ 1 GΩ (after damp heat test)
Rated current per contact	depends on mating connector A
Rated voltage	50 V

#### Mechanical

Cable O.D.	4 - 7 mm
Lifetime	> 1000 mating cycles
Wire size	1 mm <sup>2</sup>
Wire size	18 AWG
Wiring	Solder contacts
RW / Straight	Yes

#### Material

Bushing	Polyacetal (POM) + PU
Contact plating	2 μm Ni (Su)
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	Polyacetal (POM)

#### Environmental

Standard compliance	IEC 60603-11 / EIA RS-453
Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +65 °C