

1-1838226-0 Product Details



1-1838226-0

TE Internal Number: 1-1838226-0


[Active](#)

Quick Disconnect Tabs, Tab Adapters & Tab Caps


[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Terminal
- Terminal Type = Tab
- Tab Type = Wire Crimp
- Insulated
- Tab Fit = 6.35 x 0.80 mm

[View all Features](#)


[Live Product Chat](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [EURO-CRIMP INSULATED BLUE MALE PUSH-ON TERMINAL 1.5m...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [Euro-Crimp Terminals and Splices](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Terminal
- Terminal Type = Tab
- [Insulation](#) = Yes
- [Tab Fit \(mm \[in\]\)](#) = 6.35 x 0.80 [.250 x .031]
- [Material](#) = Brass
- [Insulation Diameter \(mm \[in\]\)](#) = 4.32 [.170] Max.
- [Finish](#) = None
- [Wire/Cable Type](#) = Regular Wire
- [Mount Angle](#) = Straight
- Insulation Support = Without
- Color = Blue
- Proprietary Name = EURO-CRIMP

Electrical Characteristics:

- [Dimple](#) = With

Body Related Features:

- [Tab Type](#) = Wire Crimp
- [Wire Range \(mm \[AWG\]\)](#) = 1.25-2.00² [16-14]
- Stud Hole = Without
- Flammability Rating = UL 94V-0
- Insulation Sleeve Material = PVC

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP


[BOOKMARK](#)


Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)