



# Interface Solutions UK Ltd.

www.interfacesolutions.uk.com

1 Fontwell Road  
Little Lever  
Bolton  
Lancashire  
BL3 1TE

Tel/Fax: 01204 708302  
tech@interfacesolutions.uk.com

## (IS AC/DC) **AC/DC Relay**

The IS AC/DC relay is a very versatile relay as it will operate on AC voltages ranging from 6 volts to 32 volts, and it will also operate on DC voltages ranging from 7.5 volts to 30 volts. The double pole relay is a simple to fit module wherever a dry contact, voltage free switching is required or where there is a need for higher than usual currents and voltages to be switched. The double pole relay is rated at 8 Amps complete with LED indication.

Voltage selection is made by link positions at the top and left of the board. For between 6 and 18V use both links in position A. For 18-24V use link 1 in position B and link 2 in position A. For 24-32V use both links in position B. Link 3, for the LED indication, must be selected for the appropriate voltage.

Supply Voltage	6 - 32 volts AC 7.5 - 30 volts DC
Coil Resistance	1100 Ohms
Nominal Current	46 mAmps
Double Pole Relay Rated at	8 Amps at 240 V AC 8 Amps at 30 V DC
Dimensions	56mm (W), 69mm (L), 30mm (H)

We recommend IS Sticky Feet Size B, self-adhesive mounting pillars to ensure a neat fixing.

