

DISTRIBUTION TERMINAL BLOCK 3 x CAGE CLAMP® connection 10 mm²

Packing unit 15 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 10 mm ²
Cross section [AWG]	24 - 8 AWG
Connection method	CAGE CLAMP® CONNECTION
Number of strands	73
Cross section [mm ²]	6 - 35 mm ²
Cross section [AWG]	10 - 2 AWG
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	125 A
Weight	55.5 g
Color	gray
Wiring type	Front-/Side-entry
No. of connection Points	4
No. of potentials	1
Height	39.5 mm
Height	1.55 in
Width	17.5 mm
Width	0.689 in
Depth	89 mm
Depth	3.507 in
Strip length from	12 mm
Strip length to	14 mm
Strip length	0.51 in
Connection type	CAGE CLAMP® / SCREW CLAMP CONNECTION
Mounting	TS 35