



Model No.	POS.1	POS.2	POS.3
1MD1	ON	NONE	ON
Term. Comm.	2-3,5-6	NONE	2-1,5-4
SCHEMATIC		OPEN	

SWITCH FUNCTION

PANEL MOUNTING

P.C. MOUNTING

SPECIFICATIONS
ELECTRICAL LIFE: 40,000 make-and-break cycles at full load.
CONTACT RESISTANCE: 10m Ω max. initial @ 2-4VDC
 100mA for both silver and gold plated contacts.
INSULATION RESISTANCE: 1,000M Ω min.
DIELECTRIC STRENGTH: 1,000 V RMS@sea level.
OPERATING TEMPERATURE: -30° C to 85° C.

MATERIALS
CASE: Dially phthalate (DAP) (UL94V-0).
ACTUATOR: Brass, chrome plated.
BUSHING: Brass, nickel plated.
HOUSING: Stainless Steel.
TERMINAL/CONTACT: Silver or gold plated.
SWITCH SUPPORT: Brass, Tin plated.

RATING:

R : 0.4 Volt-Amps(VA) max. @20V max.(AC or DC)
 Q : 2Amps @250VAC
 5Amps @120 VAC or 28 VDC

符號	原尺寸	修改後尺寸	變更日期
1	(A)		
2	(B)		
3	(C)		
4	(D)		
5	(E)		

SCALE (比例):	3 : 2
TOLERANCE (公差):	0.00 mm ± 0.25mm
ANGULAR:	± 2.54 mm
FILE NAME:	1MDP0045

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.

TITLE 圖名	Miniature Toggle Switches	SIZE 圖紙	A4
DWG NO. 圖號	1MD1T2B4M6RE	UNIT 單位	inch
REV. 版本	A	DATE 日期	MAR - 13 - 2002
CHECKED BY 審核	Aber Chen	DRAWN BY 製圖	BOBO
SHEET 張數	1 of 1		