



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER		TAB SIZE	WIRE RANGE mm ²	DIMENSIONS mm		
PREFIX	PK			A ±.4	B ±.3	C ±.3
DMNF1-285F1B	-C -M	2,8 X 0,5 (.110 X .020)	0,5-1,0 (22-18)	18,0 (.71)	4,8 (.19)	4,1 (.16)
DMNF1-288F1B	-C -M	2,8 X 0,8 (.110 X .032)	0,5-1,0 (22-18)	18,0 (.71)	4,8 (.19)	4,1 (.16)



NOTES:

- USED FOR:
A. 600V MAX. VOLTAGE RATING.
B. 125° C (257°F) MAX. TEMP. RATING
C. STRANDED COPPER WIRE ONLY.
- PACKAGE QTY:
A. STD: C=100
B. BULK: M=1000
- MATERIAL:
A. STAMPING: CDA 260 BRASS, TIN PLATED
B. HOUSING: TYPE 6/6 NYLON, TRANSLUCENT RED
- WIRE STRIP LENGTH: 5,6 ^{+.8}/₋₀ (7/32 ^{+1/32}/₋₀)
- FIRST INSERTION FORCE: 53N (12 LB.) MAX
FIRST WITHDRAWAL FORCE: 53N (12 LB.) MAX
27N (6 LB.) MIN
- INSTALLATION TOOLS: REF. DWGS.
A41522, A41523, A41524, A41525
- DIMENSIONS IN BRACKETS ARE IN INCHES OR AWG.



06	11/04	KLFU		ADDED GEOMETRY					A41506_06
05	6/98	TM	RLS	UPDATED PART NUMBERS AND WIRE RANGE	07035	DBH	LA		
04	10/97	JAMB	WJB	CHANGED PERIODS TO COMMAS ON ALL METRIC DIMENSIONS.	06433	DH	LA		
03	4/92	BK	RLS	SWITCHED TAB SIZES FILE SPEC WAS NPC_A41506_02	01493	KS	LA		
02	1/92	BK	RS	CHANGED COMMAS TO PERIODS, KG TO N #6 WAS A41511, #1C ADDED COPPER	00765	KS	LA		
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY JMV	CHK'D LM
								SCALE NONE	DRAWING NO./CAD FILENAME A41506

PANDUIT CORP.
TINLEY PARK, ILLINOIS
0,5 -1,0 mm²; 2,8 TAB
METRIC FULLY INSULATED FEMALE DISCONNECT