

433MHz Flexible Whip Antenna

Electrical Specifications

Frequency Range:	430-470MHz
Nominal Impedance:	50 ohm
Maximum Input Power:	50W
Polarization:	Omni
VSWR:	≤ 1.5
Connector:	SMA male straight or Right angle

Mechanical Specifications

Material:	Rugged Antenna
Antenna dimensions:	130mm x 10mm (MS) Straight 130mm x 10mm (MR) Right Angle
Antenna weight:	7g (MS) 9g (MR)
Ambient temperature:	-40 °C+ 60 °C

Order Code: ANT-433MS

ANT-433MR

