

## TradeMaster® Spec Grade 15 Amp Duplex GFCI, White - 1595W



TradeMaster/Spec Grade GFCI Receptacle with high-impact-resistant thermoplastic construction. It has SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. It prevents the line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. Its mounting screws are shipped captive in the device and wall plate for easier installation. 10kA SCCR, 15A 125VAC, White

### FEATURES

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal. Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. Extra-long strap.
- Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate. Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

### Specifications

#### DIMENSION INFO

Width U S: 1.72"

Depth U S: 0.98"

Height U S: 4.2"

1595W

**LISTING AGENCY INFO**

cULus

UL 39121614

**BUY AMERICAN ACT COMPLIANCE**

Country of Origin: CHINA

Buy American Act Status: No