

# US-601 - USB RS422/485 8 WAY HUB

## CONNECT, CONFIGURE, CONTROL YOUR SERIAL DEVICES



### Features

- 8 port RS422/485
- 128 Byte Tx and 256 Byte Rx FIFOs
- Up to 921,600 Baud
- 8xDB9 Connector (9 Pin Male) USB Type B High Retention connector (9 Pin Male)
- Rugged metal enclosure (IP30 rated)
- Drivers for all popular operating systems
- Supplied with USB cable
- Supplied with rubber feet for office environment
- Optional DIN rail mounting kits
- Lifetime Warranty\* and Lifetime Support

\* Registration required

### Descriptions


USB to Serial providing 1 RS422/485 serial port multiplexed 8 times for multibus applications. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 256 byte receive FIFOs, coupled with 1Mbit line drivers deliver uncompromising performance on your laptop/PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows XP, Server 2003, Vista, Server 2008 and Windows 7.

USB to serial is the quick low cost way to connect your computer to a serial comms enabled device. Boost software gives industry leading functionality and compatibility.


These products do away with traditional issues with USB technology so you can buy with confidence!

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!


### Example Application




CNC Machine



Point of Sale




Oil Rig



Laboratory

# US-601 - USB RS422/485 8 WAY HUB

## Box Information



## Device Dimensions

Size - 215(l) x 130(w) x 57(h) mm, 8.46(l) x 5.12(w) x 2.24(h) inches

## Port

<b>Ports</b>	8 x RS422/485
<b>Connector</b>	8xDB9 Connector (9 Pin Male) USB Type B High Retention connector (9 Pin Male)
<b>FIFO Size</b>	256 RX FIFO + 128 TX FIFO
<b>Operating Distance</b>	RS422/485 Standard (4000 ft : 1200 metres)
<b>Cable</b>	USB cable Type A to B (1 metre ~ 3ft)

## Port Settings

<b>Baud Rate</b>	921,600
<b>Data Bits</b>	7 or 8
<b>Parity</b>	Odd, Even, None, Mark or Space
<b>Stop Bits</b>	1 or 2
<b>Flow Control</b>	RTS/CTS, XON/XOFF
<b>Tx/Rx Modes</b>	Full Duplex, Half Duplex Autogating

# US-601 - USB RS422/485 8 WAY HUB

## Product Information

Power Consumption	1A@5V
Product Weight	0.761 kg, 1.68 pounds

## Interface

OS Compatibility	Microsoft Windows 7 32 bit & 64 bit Editions Windows Server 2008 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions
BUS	USB 2.0



## Approvals

Industry Approvals	Microsoft Certified Gold Partner WEEE RoHS
Microsoft Approvals	AEO C-TPAT
Microsoft Signed Drivers	Windows 7 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions



## Packing Information

Packaging	Installation CD including manual, Microsoft signed drivers & utilities
Device	USB RS422/485 8 WAY HUB
Optional Extras	Wall Mounting kit for 4&8 ports - MK-059 Snap In DIN Clip kit for 4&8 ports - MK-070 Global Power Supply - PW-500
Packaged Weight	0.125 kg, 0.28 pounds
Packaged Dims	150(l) x 145(w) x 44(h) mm, 5.91(l) x 5.71(w) x 1.73(h) inches

## Product Support

Warranty	Lifetime - online registration required
Support	Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team



# US-601 - USB RS422/485 8 WAY HUB

## Additional Information

<b>OEM option</b>	Available for bulk buy OEM
<b>Made In</b>	Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards 'Manufacturer of the Year'
<b>Customisable</b>	Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users. More info: <a href="mailto:sales@brainboxes.com">sales@brainboxes.com</a>

## Optional Extras

**ORDER CODE - Wall Mounting kit for 4&8 ports - MK-059**

**Snap In DIN Clip kit for 4&8 ports - MK-070**

**ORDER CODE - Global Power Supply - PW-500**

