

# Dynamic Speaker

## SAE-20A



- Surface Mount Design
- Low Profile
- High SPL
- Tape and Reel Packaging
- Flat Frequency Profile

### Specifications:

SPL (0.5W/10cm)	90 ± 3 dB
Rated Input	0.5 W (2.00V <sub>RMS</sub> )
Max Input	0.8 W (2.53V <sub>RMS</sub> )
Impedance	8 ± 1.6 Ω
Resonance Frequency	800 ± 100 Hz
Operation Temp.	-30°C to +85°C
External Size	15 x 15 x 4 mm
Mass	1.6 g

