



Model No.	POS.1	POS.2	POS.3
2MS1	ON	NONE	ON
Term. Comm.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING

P.C. MOUNTING

SPECIFICATIONS

ELECTRICAL LIFE: 30,000 make-and-break cycles at full load.
CONTACT RESISTANCE: 20m Ω max. Initial @ 2-4VDC
 100mA for both silver and gold plated contacts.
INSULATION RESISTANCE: 1,000M Ω min.
DIELECTRIC STRENGTH: 1,000 V RMS@sea level.
OPERATING TEMPERATURE: -30° C to 85° C.

MATERIALS

CASE - Dailiy| phthalate(DAPY UL94V-0)
ACTUATOR - Brass, chrome plated
BUSHING - Brass, nickel plated
HOUSING - Stainless Steel
SWITCH SUPPORT - Brass, tin plated.
TERMINALS/CONTACT - Brass, with Silver or gold plated.

符號	原尺寸	修改後尺寸	變更日期
1	(A)		
2	(B)		
3	(C)		
4	(D)		
5	(E)		

SCALE (比例) : 3 : 2

TOLERANCE (公差) :

0.00 mm ± 0.25mm

0.0 mm ± 0.40mm

ANGULAR : ± 2.54 mm

FILE NAME : 2MSP0029

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.

TITLE 圖名	Sub - Miniature Toggle Switches	SIZE 圖紙	A4
DWG NO. 圖號	2MS1T2B2M2RE	UNIT 單位	inch
REV. 版本	A	DATE 日期	MAR - 04 - 2002
CHECKED BY 審核		DRAWN BY 製圖	BOBO
		SHEET 張數	1 of 1

RATING :

R : 0.4 Volt-Amps(VA) max. @20V max.(AC or DC)
 Q : 1Amp @250VAC
 3Amps @120 VAC or 28 VDC